



Representative Image

Catalog No. 9T21S1050

Description: 1A,5kVA,480-120/240,115C,3R,SC8,QMS

UPC No 783173012093

Home > Transformers > Dry Type Vented > Servicenter

ABB's Single phase integrated main breaker load center with encapsulated dry type transformer ranging from 5 kVA to 25 kVA. Includes breakers for primary input and secondary output.

Descriptors

Category	Servicenter
GO Schedule	TF

Specifications

TransType	QMS
Phase	1
PriVoltage	480
SecVoltage	120/240
KVA	5.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
Sub Type	Servicenter (NEMA 3R)
Frequency	60 Hz
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	103
Outline	303B915AAP005

Classifications

UL	Yes
cUL	No
CE	No

