



Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Snap limit switch operator
Device short name	9007AO/CO

Complementary

Operator profile	Plunger head
Fixing Mode	By the head
Movement of operating head	Linear
Product Compatibility	Snap basic limit switch
Type of operator	Spring return roller plunger steel
Switch actuation	By 30° cam
Type of approach	2 directions traverse approach
Width	0.83 in (21.08 mm)
Height	2.5 in (63.50 mm)
Depth	1.6 in (40.64 mm)
Net Weight	0.1 lb(US) (0.05 kg)

Environment

NEMA degree of protection	NEMA 1 Nema type 250
IP degree of protection	IP20 conforming to IEC 60529
Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)

Ordering and shipping details

Category	21491-9007 A SNAP SWITCHES
Discount Schedule	DS1
GTIN	785901045670
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	1.60 oz (45.359 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------