



Main

Range of Product	9007
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	9007T/FT
Associated head	9007CS9 9007T10S9 9007NS9 9007AS9 9007BS9 9007T5S9
Associated complete product	9007FT 9007T 9007C..S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 2.5 in (63.50 mm) - convertible roller
Type of roller	1 steel outside roller (convertible) 1 in (25.40 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)
Ambient Air Temperature for Storage	-10...185 °F (-23...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21494-9007 ARMS FOR FT,T
Discount Schedule	DS1
GTIN	785901759829
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.80 in (2.032 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	3.50 in (8.89 cm)
Package 1 Weight	3.68 oz (104.326 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------