



Main

Range of Product	9007
Series name	Heavy duty
Device short name	C
Head type	Rotary head
Type of operator	Spring return lever arm standard pre-travel) to be ordered separately
Switch actuation	CW and CCW
Contacts type and composition	1 NO/1 NC
Contact operation	Snap action

Complementary

Body Material	Zinc alloy
Switch Function	SPDT-DB
Contact form	Form Z
Contacts material	Silver alloy (Ag/Ni)
Minimum torque for tripping	4 lbf.in (0.45 N.m)
[Ie] rated operational current	10 A, A600 10 A, Q600
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	600 V
Local signalling	1 LED load energised)
Product Certifications	CE CSA UL Listed
Provided equipment	Receptacle

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901191599
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.80 in (9.652 cm)
Package 1 Width	5.80 in (14.732 cm)
Package 1 Length	8.70 in (22.098 cm)
Package 1 Weight	24.32 oz (689.46 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------