



Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch base
Device short name	9007C
Body type	Standard plug-in
Product Compatibility	9007C
Electrical connection	Screw-clamp terminals AWG 22...AWG 12), 1...2
Cable entry	1 entry for 1/2" - 14 NPT ANSI B1.20.1
Ambient air temperature for operation	-20...185 °F (-29...85 °C) standard environment
Environmental characteristic	Standard environment
Sale per indivisible quantity	1

Complementary

Associated head	9007C
Associated connection component	9007CO62 9007CO66 9007CO68
Body Material	Zinc
Function Available	-
Mechanical durability	10000000 cycles
Width	1.55 in (39.37 mm)
Height	3.14 in (79.76 mm)
Depth	0.9 in (22.86 mm)
Net Weight	1.06 lb(US) (0.48 kg)

Environment

Shock resistance	60 gn 9 ms IEC 60068-2-27
Vibration resistance	25 gn 10...150 Hz)IEC 60068-2-6
NEMA degree of protection	NEMA 1 Nema type 250 NEMA 2 Nema type 250 NEMA 4 Nema type 250 NEMA 6 Nema type 250 NEMA 6P Nema type 250 NEMA 12 Nema type 250 NEMA 13 Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Electrical shock protection class	Class 0 IEC 61140
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Protective treatment	Epoxy powder coat

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901500896
Nbr. of units in pkg.	1
Package weight(Lbs)	7.68 oz (217.724 g)

Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.60 in (4.064 cm)
Package 1 width	2.70 in (6.858 cm)
Package 1 Length	4.10 in (10.414 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------