



## Main

|                             |                                                              |
|-----------------------------|--------------------------------------------------------------|
| Range of Product            | 9007                                                         |
| Series name                 | Heavy duty                                                   |
| Product or Component Type   | Limit switch lever                                           |
| Device short name           | 9007C                                                        |
| Associated head             | 9007C<br>9007A<br>9007B<br>9007N<br>9007T5<br>9007T10        |
| Associated complete product | 9007C<br>9007AW                                              |
| Movement of operating head  | Rotary                                                       |
| Type of operator            | Cast zinc spring return roller lever 2.5 in (63.50 mm)<br>-- |
| Type of roller              | 1 steel outside roller 0.75 in (19.05 mm) 0.25 in (6.35 mm)  |
| Type of approach            | Lateral approach                                             |
| Positive opening            | Without                                                      |

## Complementary

|                  |                      |
|------------------|----------------------|
| Switch actuation | By 30° cam           |
| Net Weight       | 0.1 lb(US) (0.05 kg) |

## Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Ambient Air Temperature for Operation | -20...185 °F (-29...85 °C) |
| Ambient Air Temperature for Storage   | -20...185 °F (-29...85 °C) |
| Environmental characteristic          | Standard environment       |

## Ordering and shipping details

|                       |                          |
|-----------------------|--------------------------|
| Category              | 21493-9007 ARMS FOR AW,C |
| Discount Schedule     | DS1                      |
| GTIN                  | 785901867920             |
| Nbr. of units in pkg. | 1                        |
| Package weight(Lbs)   | 1.60 oz (45.359 g)       |
| Returnability         | Yes                      |
| Country of origin     | MX                       |

## Packing Units

|                              |                   |
|------------------------------|-------------------|
| Unit Type of Package 1       | PCE               |
| Package 1 Height             | 0.50 in (1.27 cm) |
| Package 1 width              | 1.00 in (2.54 cm) |
| Package 1 Length             | 3.50 in (8.89 cm) |
| Unit Type of Package 2       | S01               |
| Number of Units in Package 2 | 100               |

|                  |                       |
|------------------|-----------------------|
| Package 2 Weight | 10.58 lb(US) (4.8 kg) |
| Package 2 Height | 5.91 in (15 cm)       |
| Package 2 width  | 5.91 in (15 cm)       |
| Package 2 Length | 15.75 in (40 cm)      |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                                 |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                               |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                               |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                                     |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|