



Main

Range of Product	L525
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	L525
Associated complete product	L525
Movement of operating head	Rotary
Type of operator	Aluminium spring return roller pin lever 5.73 in (145.54 mm) belt conveyor monitoring cylindrical roller pin
Type of roller	1 nylon lateral roller 1.25 in (31.75 mm)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By shifting conveyor belt
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21519-9007 MISCELLANEOUS
Discount Schedule	DS1
GTIN	785901096665
Nbr. of units in pkg.	1
Package weight(Lbs)	4.80 oz (136.078 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.40 in (3.556 cm)
Package 1 width	1.40 in (3.556 cm)
Package 1 Length	5.90 in (14.986 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------