



### Main

Device short name	XCSTE
Enclosure type	Dust and damp proof enclosure indoor/outdoor Corrosion resistance enclosure indoor/outdoor

### Complementary

Line Rated Current	6 A
[Us] rated supply voltage	120 V
Actuator	Key
Contact operation	Slow-break
Contacts type and composition	2 NC
Depth	1.3 in (33.02 mm)
Electromagnet interlocking	Locking on energisation and unlocking on de-energisation of solenoid
Enclosure material	Plastic
Height	3.67 in (93.22 mm)
Locking options description	With interlocking, locking by solenoid With locking of actuator, unlocking by key operated lock
Number of poles	2
Permissible voltage	300 V AC

### Environment

Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
IP Degree of Protection	IP67
NEMA degree of protection	NEMA 4/4X/12

### Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110825527
Returnability	No
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	4.20 in (10.668 cm)
Package 1 Length	4.60 in (11.684 cm)
Package 1 Weight	15.52 oz (439.989 g)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------