



## Main

|                                    |                   |
|------------------------------------|-------------------|
| Accessory / separate part category | Cabling accessory |
| Accessory / Separate Part Type     | Jumper cable      |

## Complementary

|                                     |                                                    |
|-------------------------------------|----------------------------------------------------|
| Jumper cable end 1                  | M12 male 5 pins straight screw-on                  |
| Jumper cable end 2                  | M12 female 5 pins straight screw-on                |
| Cable composition                   | 4 x 0.34 mm <sup>2</sup> + 1 x 0.5 mm <sup>2</sup> |
| Cable length                        | 3.28 ft (1 m)                                      |
| Wire insulation material            | PUR                                                |
| Cable outer diameter                | 0.23 in (5.9 mm)                                   |
| [Ue] rated operational voltage      | 30 V AC<br>36 V DC                                 |
| Line Rated Current                  | 4 A                                                |
| Insulation resistance               | >= 1000 MOhm                                       |
| Maximum resistance across terminals | 5000 mOhm                                          |
| Net Weight                          | 0.18 lb(US) (0.08 kg)                              |

## Environment

|                                       |                                                                       |
|---------------------------------------|-----------------------------------------------------------------------|
| IP Degree of Protection               | IP67<br>IP65<br>IP69K                                                 |
| Product Certifications                | cULus                                                                 |
| Ambient air temperature for operation | -31...194 °F (-35...90 °C) static<br>23...194 °F (-5...90 °C) flexing |
| Ambient Air Temperature for Storage   | -31...212 °F (-35...100 °C)                                           |

## Ordering and shipping details

|                   |                      |
|-------------------|----------------------|
| Category          | 22483-MACHINE CABLES |
| Discount Schedule | DS3                  |
| GTIN              | 3389110761511        |
| Returnability     | No                   |
| Country of origin | CZ                   |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Number of Units in Package 1 | 1                      |
| Package 1 Height             | 1.34 in (3.4 cm)       |
| Package 1 Width              | 5.98 in (15.2 cm)      |
| Package 1 Length             | 5.39 in (13.7 cm)      |
| Package 1 Weight             | 2.19 oz (62.0 g)       |
| Unit Type of Package 2       | S02                    |
| Number of Units in Package 2 | 20                     |
| Package 2 Height             | 5.91 in (15.0 cm)      |
| Package 2 Width              | 11.81 in (30.0 cm)     |
| Package 2 Length             | 15.75 in (40.0 cm)     |
| Package 2 Weight             | 3.50 lb(US) (1.589 kg) |


## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                                  |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                            |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                                |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                                   |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                              |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                              |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                                    |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                                                                                                                                          |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Dimensions



L : Length of cable

## Connections and Schemes

