



## Main

|                            |  |
|----------------------------|--|
| Range of Product           | Telemecanique Limit switches XC Standard   |
| Series name                | Standard format  |
| Product or Component Type  | Limit switch head  |
| Device short name          | ZCE  |
| Head type                  | M12 plunger head   |
| Product Compatibility      | XCKT<br>XCKP<br>XCMD<br>XCKD   |
| Associated body            | ZCMD29C12<br>ZCMD81L5<br>ZCMD39L5<br>ZCMD37L2<br>ZCMD69C12<br>ZCMD37L5<br>ZCMD21L08R12<br>ZCMD39L2<br>ZCMD39L1<br>ZCMD25L1<br>ZCMD41L2<br>ZCMD61M12<br>ZCMD29L1<br>ZCMD21L5<br>ZCMD41L5<br>ZCMD25L5<br>ZCMD21C12<br>ZCMD61C12<br>ZCMD81L2<br>ZCMD21L2<br>ZCMD29L5<br>ZCMD37L1<br>ZCMD21M12<br>ZCMD81L1<br>ZCMD25L2<br>ZCMD29L2<br>ZCMD21L1<br>ZCMD41L1<br>ZCMD21L08U78 |
| Movement of operating head | Linear   |
| Type of operator           | End plunger spring return metal  |
| Type of approach           | Vertical approach, 1 direction   |

## Complementary

|                  |      |
|------------------|------|
| Positive opening | With |
|------------------|------|

## Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C) |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C) |
| Environmental characteristic          | Standard environment       |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

|                   |                                    |
|-------------------|------------------------------------|
| Category          | 22413-LIMIT SWITCH, IEC, MINIATURE |
| Discount Schedule | T                                  |
| GTIN              | 3389110190908                      |
| Returnability     | Yes                                |
| Country of origin | ID                                 |

## Packing Units

|                              |                  |
|------------------------------|------------------|
| Unit Type of Package 1       | PCE              |
| Number of Units in Package 1 | 1                |
| Package 1 Height             | 0.59 in (1.5 cm) |
| Package 1 Width              | 1.30 in (3.3 cm) |
| Package 1 Length             | 0.59 in (1.5 cm) |
| Package 1 Weight             | 1.09 oz (31.0 g) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>  |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|