



MODEL: CUSA-T80-120-2200-W | DESCRIPTION: ULTRASONIC SENSOR

FEATURES

- aluminum housing
- transmitter
- open type
- wire leads




SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
type	transmitter				
operating voltage				160	Vp-p
frequency		29.5	30.5	31.5	kHz
sound pressure level		100			dB
directivity	at -6 dB	65	80	95	degree
capacitance	at 1 kHz	1,650	2,200	2,750	pF
detectable range		0		12	m
dimensions	Ø9.8 x 7				mm
material	aluminum				
terminal	wire leads				
weight			0.94		g
operating temperature		-20		80	°C
storage temperature		-20		80	°C
RoHS	yes				

MECHANICAL DRAWING


units: mm

wire: UL1571, 30 AWG




BEAM PATTERNS

SPL vs. Frequency



Directivity



REVISION HISTORY

rev.	description	date
1.0	initial release	08/09/2024
1.01	CUI Devices rebranded to Same Sky	09/12/2024

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com