



MODEL: SP-25401 | **DESCRIPTION:** AUDIO PLUG

FEATURES

- 4 conductor
- modular strain relief




SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
contact resistance				30	mΩ
insulation resistance	at 500 Vdc	100			MΩ
voltage withstand	at 50/60Hz for 1 minute			500	Vac
operating temperature		-25		70	°C
RoHS	yes				

MECHANICAL DRAWING

units: mm
tolerance: $\pm 0.3\text{mm}$
unless otherwise specified



	MATERIAL	PLATING
tip	brass	nickel
insulator	PQM	black color
sleeve	brass	nickel
tip terminal	brass	nickel
ring (1) terminal	brass	nickel
ring (2) terminal	brass	nickel
earth terminal	brass	nickel
terminal insulator	PQM	black color
body	PVC or TPR	black color

Note: 1. All specifications measured at 10~35°C with a relative humidity of 45~85% under standard atmospheric pressure unless otherwise specified.

REVISION HISTORY

rev.	description	date
1.0	initial release	05/05/2011
1.01	body material changed to TPR	08/30/2013
1.02	brand update	10/11/2019
1.03	logo, datasheet style update	01/25/2023
1.04	CUI Devices rebranded to Same Sky	09/12/2024

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com