


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/12/2023	SREITER	GUTTADAURO



NOTES:

1. PLUG: NEMA 5-15P, BLACK
2. CONNECTOR: C13 LOCK PLUS, BLACK
3. CORDAGE: SJT3X14AWG, BLACK
4. FOR REFERENCE ONLY:
 - A. COLOR CODING OF CONDUCTORS: BLACK, WHITE, GREEN
 - B. APPROVALS: UL/CSA
 - C. RATING: 15A/125V
5. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
6. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

TABULATION BLOCK	
ITEM NO.	LENGTH $\pm .6$ [15]
C13LPN515P-15-3F	36.0 [914]
C13LPN515P-15-6F	72.0 [1829]
C13LPN515P-15-10F	120.0 [3048]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com™ an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936		
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY SREITER		05/12/2023		CATEGORY		POWER PRODUCTS		
		CHECKED BY DGUST		05/12/2023						
		APPROVED BY GUTTADAURO		05/12/2023						
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				PRODUCT DESCRIPTION				
						IEC LOCK C13+ TO NEMA 5-15P, 15A, 125V				
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		ITEM NO. C13LPN515P-15		REV. A
				SCALE: NONE		CAD FILE: C13LPN515P-15-10F.SLDDRW		SHEET 1 OF 1		