



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/11/2023	SREITER	GUTTADAURO



NOTES:

1. PLUG: TYPE CEE7/VII (RIGHT-ANGLED), BLACK
2. CONNECTOR: C19 LOCKING, BLACK
3. CORDAGE: H05VVF3G1.5mm², BLACK
4. FOR REFERENCE ONLY:
 - A. COLOR CODING OF CONDUCTORS: BLUE, BROWN, GREEN/YELLOW
 - B. APPROVALS: VDE, ENEC
 - C. RATING: 16A/250V
5. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
6. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

TABULATION BLOCK	
ITEM NO.	LENGTH ±.6 [15]
C19LSCHRA-16-1M	39.4 [1000]
C19LSCHRA-16-2M	78.7 [2000]
C19LSCHRA-16-3M	118.1 [3000]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] THIRD-ANGLE PROJECTION 	APPROVALS	DATE	L-com™ an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY SREITER	05/11/2023		CATEGORY POWER PRODUCTS	
	CHECKED BY DGUST	05/11/2023			
	APPROVED BY GUTTADAURO	05/11/2023			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION IEC LOCK C19 TO R/A SCHUKO, 16A, 250V			
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321		ITEM NO. C19LSCHRA-16	REV. A
		SCALE: NONE		CAD FILE: C19LSCHRA-16-3M.SLDDRW	SHEET 1 OF 1