


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/10/2023	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-PM15FCAFCA-0-01	1.0 [3.28]
FCA-PM15FCAFCA-0-02	2.0 [6.56]

PERFORMANCE SPECIFICATIONS:

WAVELENGTH: 1550 nm.
INSERTION LOSS: ≤0.9 dB.
RETURN LOSS: ≥40 dB.
EXTINCTION RATIO AT 23°C: 23 dB MIN (25 dB TYP).
KEY ORIENTATION: SLOW AXIS.

AXIS ALIGNMENT: ±3°. PM FIBER, CONNECTOR KEY ARE ALIGNED WITH SLOW AXIS (FAST AXIS IS NOT CUT OFF).

OPERATING TEMPERATURE: -20°C TO +70°C.
STORAGE TEMPERATURE: -40°C TO +80°C.

FIBER TYPE: PM1550.
ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)





DIAGRAM OF END FACE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS .XX = ±.02 [.5] ± 1/32 .XXX = ±.005 [.13] ANGLES ± 1°	APPROVALS	DATE	L-com™ an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY KGLEBOVA	03/01/2023			CATEGORY
	CHECKED BY DFRISIELLO	03/07/2023			
	APPROVED BY PHOSPODAR	03/10/2023			
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION FIBER OPTIC PATCH CABLE, SIMPLEX POLARIZED MAINTAINING (PM) FC APC TO FC APC, 1550NM, .25MM BARE FIBER		
COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. FCA-PM15FCAFCA-0	REV. A
		SCALE: NONE		CAD FILE: fca-pm15fcafca-0.SLDDRW	
		SHEET 1 OF 1			