


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2021	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-S2SR-FCAFCA-01M	1.0 [3.28]
FCA-S2SR-FCAFCA-02M	2.0 [6.56]
FCA-S2SR-FCAFCA-03M	3.0 [9.84]
FCA-S2SR-FCAFCA-05M	5.0 [16.40]
FCA-S2SR-FCAFCA-10M	10.0 [32.81]
FCA-S2SR-FCAFCA-15M	15.0 [49.21]

NOTES:

- FC CONNECTOR ASSEMBLY POLISH TYPE: APC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY MVEERAPPAN	09/28/2021		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CHECKED BY DFRISIELLO	09/28/2021	CATEGORY FIBER OPTICS	
	APPROVED BY PHOSPODAR	09/28/2021		
PRODUCT DESCRIPTION CA FCA-FCA 9/125 SINGLEMODE			REV. A	
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321		ITEM NO. FCA-S2SR-FCAFCA
SCALE: NONE		CAD FILE: FCA-S2SR-FCAFCA.SLDDRW		SHEET 1 OF 1