


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2021	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-S2SR-FCAFCU-01M	1.0 [3.28]
FCA-S2SR-FCAFCU-02M	2.0 [6.56]
FCA-S2SR-FCAFCU-03M	3.0 [9.84]
FCA-S2SR-FCAFCU-05M	5.0 [16.40]
FCA-S2SR-FCAFCU-10M	10.0 [32.81]
FCA-S2SR-FCAFCU-15M	15.0 [49.21]

NOTES:

- FC CONNECTOR 1 ASSEMBLY POLISH TYPE: APC.
FC CONNECTOR 1 ASSEMBLY POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP
INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY MVEERAPPAN		09/28/2021			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]		CHECKED BY DFRISIELLO		09/28/2021			
THIRD-ANGLE PROJECTION 		APPROVED BY PHOSPODAR		09/28/2021			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY		FIBER OPTICS			
PRODUCT DESCRIPTION		CA FCA-FCU 9/125 SINGLEMODE					
THIRD-ANGLE PROJECTION		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. FCA-S2SR-FCAFCU	REV. A
				SCALE: NONE		CAD FILE: FCA-S2SR-FCAFCU.SLDDRW	
						SHEET 1 OF 1	