


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/21/2023	DMAY	DGUTTADAURC



- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL, APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 - DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

PART NUMBER	LENGTH	
	FEET	METERS
LUSBDVI-MM-05M	1.64	0.5±.03
LUSBDVI-MM-1M	3.28	1.0±.03
LUSBDVI-MM-2M	6.56	2.0±.03
LUSBDVI-MM-3M	9.84	3.0±.03

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div>L-com™</div> <div>an INFINIT® brand</div>		50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936					
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]		DRAWN BY DMAY		03/21/2023		CATEGORY <div>AUDIO/VIDEO</div> PRODUCT DESCRIPTION USB C TO DVI, SILVER ALUMINUM SHELL WITH BLACK NYLON BRAIDED CABLE, 1080P @ 60Hz							
		CHECKED BY HBAKKE		03/21/2023									
		APPROVED BY DGUITADAURO		03/21/2023									
THIRD-ANGLE PROJECTION <div></div>		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				SIZE A		CAGE CODE 43321		ITEM NO. LUSBDVI-MM		REV A	
						SCALE: NONE		CAD FILE: LUSBDVI-MM.SLDDRW				SHEET 1 OF 1	