

6

5

4

3

2

1

## REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	11/21/2024	HBAKKE	GUTTADAURO

F

E

D

C

B

A

F


E

D

C

B

A

CONNECTION  
DIAGRAM

P1	P2
1	1 WHITE/ORANGE
2	2 ORANGE
4	8 BLUE
5	7 WHITE/BLUE
6	3 WHITE/GREEN
7	4 GREEN
9	5 WHITE/BROWN
10	6 BROWN
S	S SHIELDED

## NOTES:

- CABLE CHARACTERISTICS:  
OPERATING VOLTAGE: 60VDC MAX  
NOMINAL VOLTAGE: 300V  
CONTACT RESISTANCE: 30mΩ MAX  
CURRENT RATING: 1.5A  
BENDING RADIUS (MOBILE): 102mm MIN  
BENDING RADIUS (FIXED): 68mm MIN  
TORSION SUPPORTED  
TEMPERATURE RANGE (MOBILE): -25°C TO +70°C  
TEMPERATURE RANGE (FIXED): -25°C TO +80°C  
DRAGCHAIN CAPABLE: YES
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

## REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

6

5

4

3

2

1

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS


TOLERANCES:  
X = ±.2 [5] FRACTIONS  
.XX = ±.02 [0.5] ± 1/32  
.XXX = ±.005 [0.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:  
≤12 [305] = +1 [25] / -0  
>12 [305] ≤ 60 [1524] = +2 [51] / -0  
>60 [1524] ≤ 120 [3048] = +4 [102] / -0  
>120 [3048] ≤ 300 [7620] = +6 [152] / -0  
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE.  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINIT@ brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

DESCRIPTION  
ix INDUSTRIAL CATEGORY 6a ETHERNET CABLE, ix A KEY TO  
M12 X-CODE FEMALE, 26AWG DOUBLE SHIELDED, DRAG CHAIN  
VW-1 FT2 PUR JACKET, GREEN

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	HBAKKE	TRGIX623PU-GRN	A