

4-Post Open Frame Rack



Our L-com 4-post open frame rack is the perfect solution to mount your large or small networking equipment in limited spaces. It's accommodating, open design is compatible with most standard 23-inch rackmount equipment and accessories. Open racks offer easy access to cables and equipment, while providing unobstructed airflow.

23in Width TIA 4-Post							
Model/SKU		LC23IN4P25U-T	LC23IN4P42U-T	LC23IN4P45U-T	LC23IN4P25U-S	LC23IN4P42U-S	LC23IN4P45U-S
PHYSICAL							
Rack Capacity (in Rack Units)		25U	42U	45U	25U	42U	45U
Rack Type		4-post	4-post	4-post	4-post	4-post	4-post
Unit Dimensions (in)	H	50.75	80.5	85.75	50.75	80.5	85.75
	W	27.3	27.3	27.3	27.3	27.3	27.3
	D	24	24	24	24	24	24
Weight Capacity (kg/ lbs.)		400kg/881lbs	400kg/881lbs	400kg/881lbs	400kg/881lbs	400kg/881lbs	400kg/881lbs
Material		Cold Rolled Steel					
Painting/ Coating		Electro-static Powder Coating - Black					
Construction		Bolted					
Rail Thread Type		Threaded 12-24			Square Hole/Cage Nut		
ADDITIONAL FEATURES							
Equipment Mounting Hardware		12-24 screws (Qty 20)	12-24 screws (Qty 40)	12-24 screws (Qty 40)	M6 screws/cagenuts (Qty 20 ea)	M6 screws/cagenuts (Qty 40 ea)	M6 screws/cagenuts (Qty 40 ea)
Mounting		Floor	Floor	Floor	Floor	Floor	Floor
Assembly		Assembly required					
COMPLIANCE AND CERTIFICATIONS							
23in width mounting standard		✓					
ROHS		✓					
CE		✓					
SHIPPING							
Shipping Dimensions (in)	L	64.2	80	85	64.2	80	85
	W	10.2	10.2	10.2	10.2	10.2	10.2
	H	28	28	28	28	28	28
Shipping Weight (lbs.)		55	77	81	55	77	81