



The L-Com AV rack cabinet is suitable for racking and storing a range of 19" equipment such as audio-visual components, servers, patch panels, PDUs, and routers.

Model / SKU Number		LC6718-1032-G-BK-Kit	LC6727-1032-G-BK-Kit	LC6737-1032-G-BK-Kit	LC6742-1032-G-BK-Kit
PHYSICAL					
Rack Capacity (in Rack Units)		18U	27U	37U	42U
Depth		700mm			
Unit Dimensions (in)	Н	38.94	54.69	72.19	80.94
	W	23.62	23.62	23.62	23.62
	D	27.72	27.72	27.72	27.72
Maximum Rail Depth (in)		24.21			
Weight Capacity (kg / lbs)		800/1763.7			
Material		Cold Rolled Steel			
Painting / Coating		Electro-Static Powder Coating - Black			
Door		Tempered Glass, Reversible Door (Includes 2x Keys)			
Interior Mounting Rails		Threaded - 10-32 screws (Includes 20x 18U & 27U, 30x 37U, 40x 42U)			
ADDITIONAL FEATURES					
Casters		Casters included (Casters add 3" to external height)			
Cable Management		Top and bottom covers screw on and off (replaceable)			
Security		Locks included for door, back, and side panels			
Cooling		Vented top for optional fan installation (purchased seperately)			
Shelving		Includes (4) 2U shelves (weight capacity 44 pounds each)			
Assembly		Assembled			
COMPLIANCE AND CERTIFICATIONS					
EIA/ECA-310-E		✓			
ROHS		✓			
CE		✓			
PCI		✓			
HIPAA		✓			
NEMA Rated Type 1		✓			
SHIPPING					
Shipping Dimensions (in)	L	30.7	30.7	30.7	30.7
	W	26	26	26	26
	Н	44.1	60	77.4	86
Shipping Weight (lbs)		148	187	223	247