

2-Post Racks



L-Com's 2-Post Desktop Mount Steel Racks are perfect for mounting your networking equipment and panels in space constrained situations. Ideal for setup on any desktop/table top environment they can also be mounted on the floor as well. Made from high quality materials this product is made to industry specifications, ensuring compatability with your equipment.

Model / SKU Number		LC-2POST-02-12U	LC-2PST-12UDSK-10-32	LC-2POST-6UDSK-10-32	LC-2POST-8UDSK-M6	LC-2POST-8UDSK-10-32
PHYSICAL						
Rack Capacity (in Rack Units)		12U	12U	6U	8U	8U
Unit Dimensions (in)	H	23	23	13	16	16
	W	20	20	20	20	20
	D	11.5	11.5	11.5	11.5	11.5
Weight Capacity (kg / lbs)		150/330				
Material		Cold Rolled Steel				
Painting / Coating		Black Powder Coating				
Construction		Bolted Assembly				
Rack Hole Type		Square Holes	Threaded (10-32)	Threaded (10-32)	Square Holes	Threaded (10-32)
ADDITIONAL FEATURES						
Casters / Floor Mount		Floor/Table Mount				
Cable Management		Available to Purchase				
Equipment Mounting Hardware		(20 Sets) M6 Cage Nuts, Screws, Plastic Washers	(6 Sets) 10-32 Screws	(6 Sets) 10-32 Screws	(20 Sets) M6 Cage Nuts, Screws, Plastic Washers	(6 Sets) 10-32 Screws
Assembly		Assembly Required				
COMPLIANCE AND CERTIFICATIONS						
EIA/ECA-310-E		✓				
ROHS		✓				
CE		✓				
DIN 41494		✓				
IEC-60297-3-100		✓				
SHIPPING						
Shipping Dimensions (in)	L	24	24	21	21	21
	W	4.13	4.13	4.3	4.3	4.3
	H	2.95	2.95	3.2	3.2	3.2
Shipping Weight (lbs)		7.6	7.6	6.4	6.9	6.9