

**RA N Male to RA N Male Cable RG-214 Coax in
48 Inch**
Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		5	GHz
VSWR			1.35:1	
Velocity of Propagation		66		%
Capacitance		30.94 [101.51]		pF/ft [pF/m]

Mechanical Specifications
Cable Assembly

Length	48 in [121.92 cm]
Diameter	0.787 in [19.99 mm]

Cable

Cable Type	RG-214
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.425 in [10.8 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male Right Angle	N Male Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material & Plating	Brass, Gold	Brass, Gold
Body Material & Plating	Brass, Nickel	Brass, Nickel

Environmental Specifications
Temperature

Operating Range -55 to +155 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data


Notes:


Configuration:

- N Male Right Angle
- N Male Right Angle
- RG-214

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data



How to Order

Part Number Configuration:

FMC4242214 - xx uu

cm = Centimeters
<blank> = Inches

Length


Example: FMC4242214-12 = 12 inches long cable
FMC4242214-100cm = 100 cm long cable

RA N Male to RA N Male Cable RG-214 Coax in 48 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [RA N Male to RA N Male Cable RG-214 Coax in 48 Inch FMC4242214-48](#)

URL: <http://www.fairviewmicrowave.com/ra-n-male-ra-n-male-cable-rg214-coax-fmc4242214-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC.
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE
RA N Male to RA N Male Cable RG-214 Coax in 48
Inch

DWG NO **FMC4242214**

CAGE CODE **3FKR5**

CAD FILE	101014	SHEET	SCALE	N/A	SIZE	A	5568
----------	--------	-------	-------	-----	------	---	------