

HMI with external touchscreen



Feature


- Full HD 1080p High Resolution HDMI™ Output
- Quad-core CPU with High Performance dedicated 3D Processor
- Plays video in high resolution, video decode 1080p H.264
- Supports customized resolution for 16:9 / 4:3 LCD monitor.
- Compact Design and DIN-rail Mountable
- Fan-less Cooling System
- Built-in 4GB Flash Memory and RTC
- One USB Host Port
- Gigabit Ethernet Port
- Supports MPI 187.5K
- Built-in Power Isolator

Memory	Flash	4 GB
	RAM	1 GB
Processor		Quad-core RISC
I/O Port	SD Card Slot	N/A
	USB Host	USB 2.0 x 1
	USB Client	N/A
	Ethernet	LAN 1: 10/100/1000 Base-T x 1 LAN 2: 10/100 Base-T x 1
	COM Port	COM1: RS-232 2W COM2: RS-485 2W/4W COM3: RS-485 2W
	RS-485 Dual Isolation	N/A
	CAN Bus	N/A
	HDMI Output	Customizable (max. resolution 1920 x 1080)
	Recommended Resolutions (Please use these recommended screen resolutions to avoid compatibility issues.)	720x480 720x576 800x600 1024x768 1280x720 1366x768 1920x1080
	Audio Output	HDMI Audio Output
RTC		Built-in
Power	Input Power	24±20%VDC
	Power Isolation	Built-in
	Power Consumption	850mA@24VDC
	Voltage Resistance	500VAC (1 min.)
	Isolation Resistance	Exceed 50MΩ at 500VDC
Specification	PCB Coating	Yes
	Enclosure	Plastic
	Dimensions WxHxD	29.8 x 130 x 115 mm
	Weight	Approx. 0.24 kg
	Mount	35mm DIN rail mounting
Environment	Protection Structure	IP20
	Storage Temperature	-20° ~ 60°C (-4° ~ 140°F)
	Operating Temperature	0° ~ 50°C (32° ~ 122°F)
	Relative Humidity	10% ~ 90% (non-condensing)
	Altitude (Air Pressure)	Below 3,000 meters (70.1kPa)
Certificate	Vibration Endurance	10 to 25Hz (X, Y, Z direction 2G 30 minutes)
	CE	CE marked
Software	UL	cULus Listed
	EasyBuilder Pro	V6.07.02 or later versions
	Weincloud	EasyAccess 2.0 (Optional), Dashboard (Optional)
	CODESYS®	Optional


* The terms HDMI, HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

* CODESYS® is a trademark of CODESYS GmbH.


Dimensions




Front View



Side View



Top View



Bottom View

a	USB Host Port	f	HDMI Port
b	LAN 2	g	DIP Switch
c	LAN 1	h	Reset Button
d	COM1: RS-232 2W, COM2: RS-485 2W/4W, COM3: RS-485 2W		
e	Power Connector		

Ordering Information

☐ cMT-FHDX-820:

4GB flash memory, 1GB RAM on board, 10/100/1000M Ethernet port x 1, 10/100M Ethernet port x 1

Optional:

- ☐ **RZ0CDS000**: CODESYS License
- ☐ **RZACEA020**: EasyAccess 2.0 Activation Card

Pin Assignment:

COM1 [RS232], COM2 / COM3 [RS485], 9 Pin, Male, D-sub

PIN#	COM1 [RS-232] 2W	COM2 [RS-485]		COM3 [RS-485] 2W
		2W	4W	
1				Data+
2	RxD			
3	TxD			
4				Data-
5	GND			
6		Data+	Rx+	
7		Data-	Rx-	
8			Tx+	
9			Tx-	