

USB-C to Dual-HDMI Adapter - USB-C or A to 2x HDMI - 4K 60Hz - 100W Power Delivery
Pass-Through - 1ft (30cm) Built-in Cable - USB to HDMI Multi-Monitor Converter for Laptop - TAA

Product ID: 109B-USBC-HDMI



Connect two 4K 60Hz HDMI displays to the USB Type-C or Type-A port of a laptop/desktop computer, using this USB-C to Dual-HDMI Adapter.

The USB video adapter features USB Power Delivery (PD) 3.0 pass-through (up to 100W), enabling powering and charging of a laptop when connected to a USB-C power adapter. The adapter runs on USB bus-power when no USB-C power adapter is connected. PD 3.0 features Fast Role Swap (FRS) that prevents USB data disruption when USB-C power is disconnected and the adapter switches to USB bus power.

The USB multi-monitor adapter is DisplayLink Certified and supports high-performance dual-monitor 4K 60Hz video resolutions with an integrated DisplayLink DL-6950 Controller.

The USB video adapter is compatible with Windows, macOS, Ubuntu, and Chrome OS. The integrated USB-C to USB-A adapter enables the flexibility of connecting to any host that is running a compatible operating system. The built-in 1ft (30cm) USB-C/A cable is ideal for on the go use. The length of the cable and the strain reliefs reduce connector/port strain.

This product is backed for 3-years by StarTech.com, including free 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility





Applications

- Run multiple applications on extended HDMI displays while charging the laptop
- Add multi-monitor capabilities, utilizing a single USB-C or USB-A connection
- Add two external displays to a workstation

Features

- **USB TO DUAL HDMI:** This USB-C or USB-A to Dual-HDMI Adapter adds up to two 4K 60Hz HDMI monitors to a computer; 100W Power Delivery pass-through with up to 90W host charging; 5.1ch HDMI Audio; 2x DisplayLink based HDMI Outputs
- **APPLE M-SERIES COMPATIBLE:** Works w/macOS enabling extended dual displays on USB-C/Thunderbolt laptops including the base Apple M-Series MacBooks, which natively only support one; Requires Driver Download for macOS
- **DISPLAYLINK CERTIFIED:** Universal Adapter works w/ Windows, macOS, Ubuntu, and ChromeOS; Automatic driver install in Windows & ChromeOS; Works with USB 3.2 Gen 1 (5Gbps), USB-C, USB4, Thunderbolt 3/4; 1ft/30cm built-in cable to reduce port/connector strain
- **EXTERNAL VIDEO GRAPHICS ADAPTER:** Connect additional displays when extra video ports are not available on the laptop or dock; Use with two external monitors and a workstation laptop screen; Ideal for business productivity apps, not ideal for gaming
- **RELIABLE PERFORMANCE:** USB bus powered or 100W PD pass-through (10W reserved for adapter + 90W for laptop charging); Prevents device dropouts, video flickering, and power overdraw; Aluminum enclosure provides EMI shielding and helps with heat dissipation

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
	USB 3.2 Gen 1 (5Gbps)
Ports	2
AV Output	HDMI
Audio	Yes

USB Pass-Through	No
Chipset ID	DisplayLink - DL6950
<hr/>	
Performance	
Maximum Digital Resolutions	3840 x 2160 @ 60Hz
Supported Resolutions	3840x2160, 2560x1440, 1920x1080, 1600x900, 1280x720 Lower resolutions may be supported
Wide Screen Supported	Yes
Audio Specifications	HDMI - 5.1 Channel Audio
<hr/>	
Connector(s)	
Connector A	1 - USB 3.2 Type-C (Power Delivery + Data, 24 Pin, Gen 1, 5 Gbps) 1 - USB Type-A (9 pin, 5 Gbps)
Connector B	2 - HDMI 1 - USB Type-C (24 pin) USB Power Delivery Only
<hr/>	
Software	
OS Compatibility	Windows 7, 8, 8.1, 10, 11, 11 ARM macOS 10.11 - 10.12, 10.14 - 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1 Ubuntu 18.04, 20.04, 22.04, 24.04 ChromeOS v55+
<hr/>	
Special Notes / Requirements	
Note	USB Power Delivery is only available when a USB-C power adapter is connected to the PD pass-through port USB-C Power Delivery is not available if using the USB-C to USB-A dongle
<hr/>	
Power	
Power Source	Bus Powered and Host USB-C Power Adapter
Laptop Charging via Power Delivery	90W

Power Consumption (In Watts) 10W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	20 to 80% RH

Physical Characteristics

Color	Gray
Material	Aluminum and Plastic
Cable Length	11.8 in [30 cm]
Product Length	4.4 in [11.3 cm]
Product Width	2.4 in [6.0 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	4.3 oz [121.0 g]

Packaging Information

Package Quantity	1
Package Length	5.6 in [14.3 cm]
Package Width	6.9 in [17.4 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	7.1 oz [200.0 g]

What's in the Box

Included in Package	1 - USB-C/USB-A to HDMI Adapter
	1 - Quick-Start Guide

Warranty Information

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

