

100W USB-C Wall Charger, 2x USB-C/2x USB-A, Quick Charging Portable GaN Charger Power Adapter, USB Power Delivery 3.0, 6ft/1.8m Cable

Product ID: 2210GCN-WALL-CHARGER



This 100W USB GaN Charger provides a versatile and powerful charging solution for USB devices. The GaN Charger features two USB-C ports (PD 3.0 100W max) and two USB-A ports (QC 3.0 24W max). The compact travel adapter is designed for quick and efficient charging. Despite its robust capabilities, it weighs just 9.7 oz (274 g), making it the perfect companion for your travels. The package includes a 6ft (1.8m) USB-C cable, ensuring you have everything you need for immediate use.

This USB Wall Charger is designed for optimal cooling, ensuring a safer and more reliable charging experience. By balancing size and functionality, we deliver a superior charging solution that prioritizes both efficiency and durability. As a result, the USB charger not only maintains its performance over longer periods but also charges devices faster.

Featuring a unique foldable 360 rotating plug, this charger provides optimal outlet positioning. The built-in North American power plug (NEMA 1-15P) can rotate a full 360 degrees, offering maximum flexibility and convenience. The foldable design not only enhances portability but also simplifies storage, ensuring it can travel anywhere without hassle.

This charger is compatible with all USB-C laptops, phones, and tablets, including popular models like the MacBook Pro/Air, iPhone 15 and up, iPad Pro, Samsung Galaxy, One Plus, Google Pixel, Samsung S20/S21, and Galaxy 20. This broad compatibility makes it a reliable choice for a wide range of devices.

Safety and efficiency are paramount with the 100W USB GaN Charger. It is ETL Safety Listed (IEC 62368-1) and FCC/ICES EMC certified, providing protection against over-voltage, current, and temperature. The Active Power Factor Correction (PF > 0.99) enhances efficiency and ensures cool operation. Additionally, it meets DOE Level VI standards, guaranteeing energy efficiency and reliable performance.

Certifications, Reports and Compatibility

Applications

- Ideal for travel with a light weight design and port variation eliminating the need to carry multiple chargers for different devices
- Power laptops and other USB devices in at the office or home office

Features

- 100W USB GaN CHARGER: 4-port USB wall charger with 2x USB-C (100W max, PD 3.0) & 2x USB-A (24W max, QC 3.0); Compact travel adapter (9.7 oz/274 g); Quick charging with multiple PD voltage profiles (5V/9V/12V/15V/20V); 6ft (1.8m) 100W USB-C Cable Included
- COOL RUNNING CHARGER: This 4-port power adapter is designed to run cool under extended full-load use; 2x USB-C ports (100W max, USB Power Delivery 3.0 support) and 2x USB-A ports (24W max, Quick Charging 3.0 support) for quick and efficient charging
- FOLDABLE 360 ROTATING PLUG: Built-in foldable North American power plug (NEMA 1-15P) rotates a full 360 degrees, allowing for optimal outlet positioning; Foldable design enhances portability and storage convenience
- BROAD COMPATIBILITY: Works to charge all USB-C laptops/phones/tablets; MacBook Pro/Air, iPhone 15 and up, iPad Pro, Samsung Galaxy, One Plus & Google Pixel, Samsung S20/S21, Galaxy 20 & other devices
- SAFE, RELIABLE & EFFICIENT: Designed to keep users & devices safe; ETL Safety Listed (IEC 62368-1) & FCC/ICES EMC certified; Over-voltage, current, and temp. protection; Active Power Factor Correction (PF > 0.99); Meets DOE Level VI standards

Hardware

Warranty	3 Years
Ports	4

Connector(s)

Input Connector(s)	1 - NEMA 1-15 Power (North America)
Output Connectors	2 - USB Type-C (24 pin) USB Power Delivery Only 2 - USB Type-A (4 pin) Power Only

Power

Input Voltage	100 - 240 AC
Input Current	2.5 A
Output Voltage	5V DC 9V DC

12V DC

15V DC

20V DC

Output Current 5 A

Plug Type NEMA 1-15 Power (North America) Plug

Power Consumption (In
Watts) 100 W

Environmental

Operating Temperature 0 to 25C (32 to 77F)

Storage Temperature -15 to 40C (5 to 185F)

Humidity 20% ~ 85% RH

Physical Characteristics

Color Black

Material Plastic

Product Length 3.0 in [7.7 cm]

Product Width 1.3 in [3.3 cm]

Product Height 2.9 in [7.4 cm]

Weight of Product 9.7 oz [274.0 g]

Packaging Information

Package Length 6.9 in [17.4 cm]

Package Width 6.1 in [15.5 cm]

Package Height 1.6 in [4.0 cm]

Shipping (Package)
Weight 1.1 lb [0.5 kg]

What's in the Box

Included in Package 1 - USB Wall Charger

1 - 6 ft. [1.8m] USB-C Cable (100W)

**Warranty
Information**

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

