

12ft (3.6m) Heavy Duty Power Cord, NEMA 5-15P to Locking C13 AC Power Cable, 15A 125V, 14AWG, Replacement Computer Power Cord, TAA Compliant, UL Listed

**Product ID:** 27LC-4B00-POWER-CORD



#### The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

#### Certifications, Reports and Compatibility



## Applications

- Locking C13 connector hinders accidental power disconnection
- Connect a computer, display, or laptop power supply to a wall outlet or PDU

## Features

- **HEAVY DUTY AC POWER CORD:** 12ft (3.66m) 14AWG Universal Power Cord with NEMA 5-15P to Locking IEC 60320 C13 connector is suitable for workstations/home office or high-power rack mounted equipment such as servers and PDUs; Indoor use; Up to 125V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; Locking C13 connector prevents accidental disconnection; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 12ft (3.66m); TAA Compliant; NEMA 5-15P to Locking IEC 60320 C13; 14AWG; 125V 15A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- **COMPATIBILITY:** NEMA 5-15P plug works with North American electrical outlets; IEC C13 connector works with most computers, monitors, and displays; Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

---

### Performance

Maximum Cable Length	12.0 ft [3.7 m]
----------------------	-----------------

---

### Connector(s)

Connector A 1 - NEMA 5-15 Power (North America)

Connector B 1 - IEC 60320 C13 Power

---

**Power**

Input Voltage 125 AC

Input Current 15A

---

**Environmental**

Operating Temperature -20 to 105C (-4 to 221F)

Storage Temperature -20 to 105C (-4 to 221F)

Humidity 0% to 65% RH

---

**Physical Characteristics**

Color Black

Connector Style Straight

Wire Gauge 14 AWG

Cable Length 12.0 ft [3.7 m]

Cable OD 0.4 in [9.3 mm]

Product Length 12.0 ft [3.7 m]

Product Width 1.2 in [2.9 cm]

Product Height 1.0 in [2.6 cm]

Weight of Product 1.2 lb [0.6 kg]

---

**Packaging Information**

Package Length 12.6 in [32.0 cm]

Package Width 4.4 in [11.2 cm]

Package Height 1.9 in [4.9 cm]

Shipping (Package) Weight 1.3 lb [0.6 kg]

---

**What's in the Box**

Included in Package

1 - 12ft NEMA 5-15P to Locking C13 Power Cord

---

**Warranty  
Information**

---

Warranty

Lifetime

---

***\*Product appearance and specifications are subject to change without notice.***

