

Citrix 3013936-E2 Compatible QSFP+ Module - 40GBASE-SR4 - Multi Mode Fiber (MMF) - 40GE Gigabit Ethernet QSFP+ - MPO 100m - 850nm - DDM

Product ID: 3013936-E2-ST



The 3013936-E2-ST is a Citrix 3013936-E2 compatible fiber transceiver module that has been designed, programmed and tested to work with Citrix brand switches and routers. It delivers dependable 40 GbE connectivity over fiber cable, for 40GBASE-SR4 compliant networks, with a maximum distance of up to 100 m (328 ft).

Technical Specifications:

Wavelength: 850nm

Maximum Data Transfer Rate: 40 Gbps

Type: Multi Mode

Connection Type: MPO

Maximum Transfer Distance: 100 m (328 ft)

MTBF: 244,610,582 hours

Power Consumption: < 0.7W

This QSFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

Features

- 100% CITRIX 3013936-E2 COMPATIBLE: Designed, programmed and tested to work with compatible Citrix switches and routers to deliver reliable 40GbE connectivity
- TECHNICAL SPECS: 40GBASE-SR4 40 Gbps Multi Mode MPO Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 100 m (328 ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Citrix routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance

Hardware

| | |
|------------------|----------|
| Warranty | Lifetime |
| Compatible Brand | Citrix |

Performance

| | |
|------------------------------|-------------------|
| Maximum Data Transfer Rate | 40.00Gbps |
| Max Transfer Distance | 100m [328ft] |
| Type | Multi Mode |
| Wavelength | 850nm |
| Compatible Networks | 40 Gbps |
| MTBF | 244,610,582 hours |
| Power Consumption (In Watts) | < 0.7W |

Physical Characteristics

| | |
|-------------------|------------------|
| Product Length | 4.8 in [12.2 cm] |
| Product Width | 0.7 in [1.8 cm] |
| Product Height | 0.4 in [1.1 cm] |
| Weight of Product | 1.4 oz [40.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 7.3 in [18.6 cm] |
| Package Width | 5.2 in [13.3 cm] |
| Package Height | 2.0 in [5.0 cm] |
| Shipping (Package) Weight | 4.5 oz [128.0 g] |

What's in the Box

| | |
|---------------------|-----------------------|
| Included in Package | 1 - QSFP+ Transceiver |
|---------------------|-----------------------|

Warranty Information

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

**Product appearance and specifications are subject to change without notice.*

