

140W USB-C Wall Charger, 3x USB-C/1x USB-A, PD 3.1 International GaN Power Adapter for MacBook/Dell XPS/Inspiron

Product ID: 3114GCU-WALL-CHARGER



This 140W USB-C GaN Charger delivers a versatile, high-power charging solution for USB-C and USB-A devices, supporting up to 140W with PD 3.1. The power adapter features 3x USB-C (140W max, PD 3.1) and 1x USB-A (12W max) charging ports to carry dedicated chargers for your laptop tablet and smartphone, this one charger can charge all your devices.

This USB Wall Charger is engineered for optimal cooling, providing a safer, more reliable charging experience. Balancing compact size with powerful functionality, the power adapter features a small foot print (3.7 in/9.6cm x 1.2in/3.08cm x 3in/7.6cm) and weighs just 12.6 oz (358 g). This travel-friendly adapter combines robust capabilities with easy portability, making it an ideal companion on the go.

The power adapter includes interchangeable power clips designed to meet regional electrical standards, ensuring reliable compatibility across multiple countries. The package includes four plug types: the NEMA 1-15P for North America, the BS 1363P for the United Kingdom, the CEE 7/16P for Europe, and the AS/NZS 3112 Australia. Each plug is engineered to maintain a secure connection and conform to its respective region's voltage and current requirements with support for 100-240V auto switching. This modular system simplifies international travel and eliminates the need for additional adapters, providing a versatile and practical solution for powering devices worldwide. A travel pouch is also included to neatly pack all the regional power clips.

Safety and efficiency are paramount with the 140W USB GaN Charger. It is TUV Safety Listed (IEC 62368-1) and FCC/ICES EMC certified, providing protection against over-voltage, current, and temperature. The Active Power Factor Correction (PF > 0.99) enhances efficiency and ensures cool operation. Additionally, it meets DOE Level VI standards, guaranteeing energy efficiency and reliable performance.

Certifications, Reports and Compatibility



Applications

- Ideal for travel with a light weight design and port variation eliminating the need to carry multiple chargers for different devices
- Power laptops and other USB devices in at the office or home office

Features

- 140W USB GaN CHARGER: USB wall charger with 3x USB-C (PD 3.1, 140W max on port 1, 65W max on port 2 & 3) and 1x USB-A (12W max) to charge your laptop, smartphone & other USB devices simultaneously; Multiple PD voltage profiles (5V/9V/15V/20V/28V up to 5A)
- COOL RUNNING AND COMPACT: Engineered for cool performance under extended full-load use; Small footprint and light weight (3.7 in/9.6cm x 1.2in/3.08cm x 3in/7.6cm, 12.6 oz/358 g) for portability and easy storage
- 16" MACBOOK PRO COMPATIBLE: PD 3.1 Power Adapter fully supports MacBook M3/M4 Pro/Max ensuring high-speed 140W charging; Charges all USB-C devices with earlier PD revisions like MacBook, Dell XPS/Precision/Inspiron, iPad Pro, iPhone & Samsung smartphones
- INTERNATIONAL TRAVEL READY: Power adapter supports 100 - 240V AC and includes interchangeable power plugs for North America (NEMA 1-15P), UK (BS 1363P), Europe (CEE 7/16P) and Australia (AS/NZS 3112); Neatly pack all the regional power clips in the included travel pouch
- SAFE, RELIABLE & EFFICIENT: Designed to keep users & devices safe; TUV Safety Listed (IEC 62368-1) & FCC/ICES EMC certified; Over-voltage, current, and temp. protection; Efficient design includes Active PF Correction (>0.99) & meets DOE Level VI standards

Hardware

Warranty	2 Years
Number of Power Outlets	4
Industry Standards	USB Power Delivery 3.1

Performance

General Specifications	Total Aggregate Power: 142.0W Max, USB-C Port #1 Output: 5.0V3.0A, 9.0V3.0A, 15.0V3.0A, 20.0V5.0A, 28.0V5A (140.0W Max)
------------------------	-------------------------------------------------------------------------------------------------------------------------------

USB-C Ports #2 & 3 (Shared) Output:

5.0V3.0A, 9.0V3.0A, 15.0V3.0A, 20.0V3.25A (65.0W Max)

PPS: 3.3-21.0V3.25A (65.0W Max)

USB-A Port Output:

5.0V2.4A (12.0W Max)

Connector(s)

Input Connector(s)	1 - NEMA 1-15 Power (North America) 1 - BS 1363 Power (UK) Plug 1 - CEE 7/16 Power (Europlug) Plug 1 - AS/NZS 3112 Power (Australia)
Output Connectors	3 - USB Type-C (24 pin) USB Power Delivery Only 1 - USB Type-A (4 pin) Power Only

Power

Input Voltage Frequency	50-60Hz
Input Voltage	100 - 240 AC
Input Current	2.2A
Power Consumption (In Watts)	142W

Environmental

Operating Temperature	0 to 25C (32 to 77F)
Storage Temperature	-20 to 80C (-4 to 176F)
Humidity	Operation: 10% ~ 90% RH Storage: 10% ~ 90% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	3.8 in [9.6 cm]

Product Width	3.0 in [7.6 cm]
Product Height	1.2 in [3.1 cm]
Weight of Product	12.4 oz [351 g]

Packaging Information

Package Length	5.8 in [14.7 cm]
Package Width	8.2 in [20.9 cm]
Package Height	2.2 in [5.7 cm]
Shipping (Package) Weight	1.2 lb [0.6 kg]

What's in the Box

Included in Package	1 - 140W Multiport International Wall Charger
	1 - NA Plug (Installed)
	1 - EU Plug
	1 - UK Plug
	1 - AU Plug
	1 - Plug Storage Bag
	1 - Product Documentation

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*