

6ft (1.8m) Heavy Duty Power Cord, Right Angle C14 to C13, PDU Power Cord, 15A 250V, 14AWG, Heavy Gauge Power Cable, TAA Compliant, UL Listed

Product ID: 8745-4600-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Extend a monitor, scanner, printer, or PC power cord by an additional 6ft
- Angled C14 connector saves space in crowded installations

Features

- **HEAVY DUTY POWER CORD:** 6ft power supply cable with Right Angle IEC 60320 C14 to Straight C13 connector connects neatly to a power supply or a PDU; 90-degree C14 connector enables convenient access in tight spaces; Rated to carry 250V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.83m); TAA Compliant; Right Angle IEC 60320 C14 to IEC 60320 C13; 14AWG; 250V 15A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.36in (9.3mm); Indoor use
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 connector works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Performance

Maximum Cable Length	6.0 ft [1.8 m]
----------------------	----------------

Connector(s)

Connector A 1 - IEC 60320 C14 Power

Connector B 1 - IEC 60320 C13 Power

Power

Input Voltage 250 AC

Input Current 15A

Environmental

Operating Temperature -20 to 105C (-4 to 221F)

Storage Temperature -20 to 105C (-4 to 221F)

Humidity 0% to 65% RH

Physical Characteristics

Color Black

Wire Gauge 14 AWG

Cable Length 6.0 ft [1.8 m]

Cable OD 0.4 in [9.3 mm]

Product Length 6.0 ft [1.8 m]

Product Width 1.7 in [4.4 cm]

Product Height 0.8 in [2.1 cm]

Weight of Product 10.7 oz [302.0 g]

Packaging Information

Package Length 9.7 in [24.7 cm]

Package Width 3.7 in [9.4 cm]

Package Height 1.9 in [4.9 cm]

Shipping (Package) Weight 10.8 oz [306.0 g]

What's in the Box

Included in Package 1 - 6ft Right Angle C14 to C13 Heavy-Duty Power Extension Cord

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

