

3m RS232 Serial Null Modem Cable, Crossover Serial Cable w/Al-Mylar Shielding, DB9 Serial COM Port Cable Female to Male, Compatible w/DTE Devices, Black, F/M

Product ID: 9FMNM-3M-RS232-CABLE



This null modem serial cable features male and female DB9 connectors. It enables a connection between serial devices at a distance of up to 3 meters. The length of the cable allows for flexible serial device setup configuration.

The crossover serial cable mitigates EMI with its high-quality shielded metal shell connectors and aluminum mylar cable shielding.

Install and secure the RS232 serial cable, using the thumbscrews. These connector screw locks prevent accidental disconnection which could lead to data loss/corruption.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **RS232 SERIAL NULL MODEM CABLE:** DB9 male to female serial cable enables a connection between two DTE devices at a distance of up to 3 meters, reducing cable length restrictions and providing flexible serial device setup configuration

- **QUALITY CONSTRUCTION:** High quality 28 AWG tinned wires with aluminum mylar cable shielding and shielded metal shell connectors prevent EMI interference; Molded PVC connectors with strain reliefs and PVC cable jacket prevent damage due to bends
- **SCREW LOCKING NULL-MODEM CABLE:** This crossover cable features thumbscrews that prevent accidental disconnection which can lead to data loss
- **SPECIFICATIONS:** 3m (9.8ft) DB9 male to DB9 female Color: Black 28AWG OD: 4.8mm Al-Mylar cable shield & Metal shell connectors Molded PVC strain reliefs and jacket Note: This is a null-modem cable, it is not a straight-through cable
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this serial null-modem DB9 cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance This serial cable is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	7
Connector Plating	Nickel
Cable Jacket Material	PVC
Cable Shield Material	Aluminum-Mylar Foil with Drain

Performance

Supported Protocols	Null modem
---------------------	------------

Connector(s)

Connector A	1 - DB-9 (9 pin, D-Sub)
Connector B	1 - DB-9 (9 pin, D-Sub)

Special Notes / Requirements

Note	This is not a straight-through serial cable
------	---

Environmental

Operating Temperature	20 to 80C (68 to 176F)
Storage Temperature	20 to 80C (68 to 176F)
Humidity	15% ~ 65%

Physical Characteristics

Color	Black
-------	-------

Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	9.8 ft [3 m]
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	5.1 oz [143.5 g]

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.7 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.9 in [2.4 cm]
Shipping (Package) Weight	5.5 oz [156.0 g]

What's in the Box

Included in Package	1 - Null Modem Serial Cable F/M
---------------------	---------------------------------

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

