

100 Pack Screw Mount Cable Clamps - Large 7.9mm Bundle Cable Fastener/Holder - R-Type Single Reusable Nylon Clip - Screw Down Ethernet Cord Management Clamp - UL/94V-2 Rated - TAA

Product ID: CBMSDCC3



These R type cable clips secure cables to the wall to route and organize them. 100 White cable clips are included, ensuring you'll have plenty on hand.

These plastic electrical cable clips feature a built-in 0.19 in. (5 mm) mounting hole enabling you to bundle cables while mounting them to a wall. They hold small cables up to 0.31 in. (7.9 mm). They're quick and easy to install or remove, with a single screw hole that secures the cable and mounts it to the wall -- perfect for organizing and routing network cables, power cables, or other cables at your home or office.

Made of durable Nylon 66 material, these cable clips are tough and flexible. They're -40 to 85C temperature rated, UL94 V-2 fire rated, UL Approved.

To suit different applications, StarTech.com offers a selection of these cable clips in different sizes:

Small for 0.19in (5 mm) cable diameter (CBMSDCC1)

Medium for 0.25in (6.35 mm) cable diameter (CBMSDCC2)

Large for 0.31in (7.9 mm) cable diameter (CBMSDCC3)

These cable clips are TAA compliant and backed by a StarTech.com 2-year warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

- Route cables while mounting them to a wall or ceiling in your office or server room

Features

- 100 PACK OF SCREW MOUNT CABLE CLAMPS: R type cable clip holds large cable bundles up to 0.31" (7.9mm) in diameter, keeping cables organized
- ORGANIZE & SECURE: Cable management fastener to mount coax, RJ11 telephone wire, AV, RJ45 CAT5/CAT6 Ethernet, network & USB cables to baseboards, wood trim, drywall or masonry w/single screw or nail
- INDUSTRIAL STRENGTH: Reusable screw down cord holder is made of durable UL Listed Nylon 66 material that is UL94 V-2 fire rated; -40 to 85C temperature rated; UL Approved; RoHS & TAA compliant
- AVAILABLE IN OTHER SIZES: Small (CBMSDNMCC1) for 0.19" (5mm) bundle diameter; Medium (CBMSDNMCC2) for 0.25" (6.35mm) bundle diameter
- STARTECH.COM ADVANTAGE: IT professionals choice for over 30 years; These cable clips are backed for 2 years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Performance

Warranty	2 Years
General Specifications	Maximum Cable Diameter: 0.31 in [7.9 mm]
	Mounting Hole Size: 0.19 in [5 mm]

Physical Characteristics

Color	White
Material	Nylon 66
Product Length	0.3 in [8.0 mm]
Product Width	0.9 in [2.3 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	0.0 oz [0.6 g]

Packaging Information

Package Quantity	100
Package Length	5.2 in [13.2 cm]

Package Width	5.7 in [14.6 cm]
---------------	------------------

Package Height	2.0 in [5.1 cm]
----------------	-----------------

Shipping (Package) Weight	2.4 oz [68.0 g]
------------------------------	-----------------

What's in the Box

Included in Package	100 - Screw Mount Cable Clamps
---------------------	--------------------------------

**Warranty
Information**

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*