

6"(15cm) Cable Ties with Mounting Hole - 1/8"(3mm) wide, 1-1/2"(40mm) Bundle Dia. 40lb(18kg)
Tensile Strength, Nylon 66 Self Locking Ties w/Screw Hole, UL Listed, 100 Pack - TAA

Product ID: CBMZTS10N6



These medium cable ties with mounting hole enable you to conveniently bundle and secure multiple cables and route and organize them. 100 White cable ties are included, ensuring you'll have plenty on hand.

These plastic electrical cable wraps feature a built-in mounting hole (5 mm in diameter) enabling you to bundle cables, then mount them to a wall. They are 6.75 in. (171.5 mm) in length securing cable bundles up to 1.57 in. (40 mm) in diameter. They're quick and easy to install or remove, with adjustable tension and a basic one-piece design -- perfect for organizing network cables, power cables, or other cables at your home or office workstation.

Made of durable Nylon 66 material, these cable ties are tough and flexible. They've been rigorously tested to support up to 40 lbs (18 kg) of weight & are UL94 V-2 fire rated, UL Approved, and CE & Lloyd's Register Certified.

To suite any application, StarTech.com offers a selection of these cable ties in different lengths:

100-pack - 4.33 in. (110 mm) White Cable Ties with Mounting Hole (CBMZTS10N4)

100-pack - 6.75 in. (171.5 mm) White Cable Ties with Mounting Hole (CBMZTS10N6)

100-pack - 8.62 in. (219 mm) White Cable Ties with Mounting Hole (CBMZTS10N8)

These cable wraps are backed by a StarTech.com 2-year warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

Features

- **100-PACK OF CABLE TIES WITH MOUNTING HOLE:** Keep cables organized with small 6" (15 cm) white zip ties for 1.57" (40mm) cable bundle diameter; self-locking zip tie, enables you to tie up cables easily; UL File Number: E97527
- **BUILT-IN MOUNTING HOLE:** Screw-down and mount coax cable, RJ11 telephone wire, audio, video, RJ45 CAT5/CAT6 network & USB cables to baseboards, wood trim, drywall or masonry with a single screw or nail
- **INDUSTRIAL STRENGTH:** Made of durable UL Listed Nylon 66 material, these cable ties are tested to support up to 40lbs (18Kg) of weight; UL94 V-2 fire rated at up to 85C; DNV-GL & ABS Approved; RoHS; TAA
- **OTHER SIZES AVAILABLE:** Mountable head tie wraps come in 4.33" (110 mm) for 0.94" (24mm) bundle diameter at 18lbs (CBMZTS10N4); 8.62" (219 mm) for 2.05" (52mm) bundle diameter at 50lbs (CBMZTS10N8)
- **STARTECH.COM ADVANTAGE:** IT professional's choice for over 30 years; These adjustable cable ties are backed for 2 years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Physical Characteristics

Warranty	2 Years
Color	White
Material	Nylon 66
Product Length	6.8 in [17.2 cm]
Product Width	0.1 in [3.7 mm]
Product Height	0.1 in [1.3 mm]
Weight of Product	0.0 oz [1.0 g]

Packaging Information

Package Quantity	100
Package Length	8.0 in [20.4 cm]
Package Width	5.4 in [13.8 cm]
Package Height	1.6 in [4.1 cm]
Shipping (Package) Weight	3.7 oz [106.0 g]

What's in the Box

Included in Package	100 - Cable Ties
---------------------	------------------

**Warranty
Information**

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

