

## 6 ft DVI to Coax High Resolution VGA Monitor Cable

**Product ID:** DVIVGAMM6



The DVIVGAMM6 6-foot DVI to VGA Monitor Cable features a DVI (analog) male connector and a VGA (High Density D-Sub) male connector, providing a cost-effective way to connect an analog or a dual mode Flat Panel Display to a PC or Mac computer with a DVI Analog Video Card.

Expertly designed and constructed of only high quality materials, the 6ft DVI to VGA Monitor cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connects PC/Mac with DVI Analog Video Card to an Analog or Dual-Mode Flat Panel Display

### Features

- Manufactured according to DVI specifications
- Molded connector ends with strain relief

---

#### Hardware

Warranty

Lifetime

---

Active or Passive Adapter	Passive
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Connector(s)**

Connector A	1 - DVI-A (17 pin)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.6 in [4.1 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	6.6 oz [186.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	7.4 in [18.7 cm]
Package Width	7.8 in [19.7 cm]
Package Height	1.1 in [2.9 cm]
Shipping (Package) Weight	6.8 oz [192.0 g]

---

**What's in the Box**

Included in Package	1 - 6 ft DVI to Coax High Resolution VGA Monitor Cable
---------------------	--

---

**Warranty Information**

Warranty

Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*

