

7 Port USB C Hub with Fast Charge Port - USB-C to 5x USB-A 2x USB-C (USB 3.0 SuperSpeed 5Gbps) - Self Powered USB 3.2 Gen 1 Type-C Hub w/ Power Adapter - Desktop/Laptop Hub

Product ID: HB30C5A2CSC



This USB-C hub turns your laptop or desktop USB Type-C or Thunderbolt 3 port into four standard USB-A ports, one USB-A fast-charge port, and two USB-C ports. You can also extend the range of your USB devices by using this hub as a mid-point repeater.

The 7-port USB hub provides convenient port access. The extended length of the supplied cable offers the flexibility to position your hub and USB devices as needed, in order to create a comfortable, space-efficient work area. The ports are sufficiently spaced to plug or unplug your USB devices without needing to disconnect other devices from neighboring ports.

With extra USB 3.2 Gen 1 ports, you can increase productivity and connect more devices to your computer, or avoid the hassle of swapping connected devices on your port-limited laptop.

The hub lets you extend the life of your current USB 3.2 Gen 1 devices while also taking advantage of newer USB-C devices.

With the available fast-charge port, the hub helps to ensure that your tablet or smartphone are charged and ready to use when you need them. You can also sync and access your device while it's charging. The USB-A charge port supports USB Battery Charging Specification 1.2.

The HB30C5A2CSC is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Upgrade and expand the connection capabilities of your MacBook, Ultrabook, laptop, or desktop
- Deploy in hot-desk environments to provide USB hub access for multiple devices
- Connect a wide variety of peripherals at home or in the office, all from a single USB 3.2 Gen 1 connection

Features

- **7 PORT USB C HUB:** From a USB 3.2 Gen 1 (5Gbps) Type-C host port, add 5x USB-A and 2x USB-C ports; Backwards compatible with USB 2.0/1.1; Includes 3.3ft (1m) USB-C host cable; Thunderbolt 3 Compatible
- **SELF-POWERED USB HUB:** Includes external 12V 4A universal power adapter (NA, EU, UK, JP, AU/NZ) & a dedicated power switch for easy power toggling of all connected downstream devices to conserve energy
- **SPEEDS UP TO 5Gbps:** USB 3.2 Gen 1 SuperSpeed shared with all downstream devices, supports thumb drives, data storage devices, keyboards, mice, web cams, headsets
- **FAST CHARGE PORT WITH BC 1.2:** Power up to 1.5A (7.5W) features a standalone Dedicated Charging Port (DCP) for hostless charging or works as a Charging Downstream Port (CDP) for data and charging
- **WIDE OPERATING SYSTEM COMPATIBILITY:** USB C laptop/desktop hub is OS Independent, driverless setup, supporting major operating systems including Windows, macOS, Linux, iPadOS, Chrome OS and Android

Hardware

Warranty	2 Years
USB-C Device Port(s)	Yes
USB-C Host Connection	Yes
Ports	7
Interface	USB 3.2 Gen 1 (5Gbps)
Bus Type	USB 3.2 Gen 1 (5Gbps)
Industry Standards	USB Battery Charging Specification Rev. 1.2
	USB-A charging port delivers up to 1.5 amps of power
	USB 3.0 - Backward compatible with USB 2.0 and 1.1

Chipset ID	VIA/VLI - VL813
------------	-----------------

Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.2 Gen 1)
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
UASP Support	Yes
Supported Charging Modes	Charging Downstream Port (CDP) Dedicated Charging Port (DCP)
Supported Charging Outputs	BC 1.2 (1.5A)

Connector(s)

Connector Type(s)	4 - USB Type-A (9 pin, 5 Gbps) 2 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps) 1 - USB 3.2 Type-A (9 pin, Fast-Charge) 1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)
-------------------	--

Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Special Notes / Requirements

System and Cable Requirements	Available USB Type-C port - USB 3.0 (5Gbps)
Note	The USB Type-C ports are data only. USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.
	The hub does not support DP Alt Mode or USB Power Delivery.

Indicators

LED Indicators	7 - Active
----------------	------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC

Input Current	1 A
Output Voltage	12V DC
Output Current	4 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	48

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~95% RH (Non-condensing) at 25C

Physical Characteristics

Color	Black & Silver
Form Factor	Desktop
Material	Plastic
Cable Length	3.3 ft [1 m]
Product Length	5.9 in [14.9 cm]
Product Width	2.6 in [6.5 cm]
Product Height	0.9 in [2.4 cm]
Weight of Product	5.3 oz [150.0 g]

Packaging Information

Package Quantity	1
Package Length	6.0 in [15.2 cm]
Package Width	8.4 in [21.4 cm]
Package Height	2.1 in [5.4 cm]

Shipping (Package)
Weight 1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - USB-C hub
	1 - 1m USB-C to USB-B cable
	1 - universal power adapter (NA/JP, UK, EU, ANZ)
	1 - quick-start guide

**Warranty
Information**

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

