

## 4 Port USB to RS232 Serial DB9 Adapter Hub - TAA

**Product ID:** ICUSB2324



This 4 Port USB to RS232 Serial Hub lets you connect up to four RS232 serial devices to your Mac or PC laptop or desktop computer through a single USB port, as though the computer offered built-on DB9M serial connectors.

The RS232 Serial Hub is compactly designed to preserve valuable workspace, and is bus-powered to eliminate the need for an external power adapter.

A cost-effective solution that bridges the compatibility gap between modern USB-capable computers and legacy RS232 serial peripherals, this dependable USB/RS232 Serial Adapter hub is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Connect modems, digitizer tablets, mice, bar code scanners, GPS receivers, ISDN terminal adapters, mobile

phones, scanners, UPSes and POS equipment to your system

- Connect and program LED and Digital signage boards with serial communication ports

## Features

- Provides you with four additional RS232 serial ports
- Fully compliant with USB 1.1 specifications and compatible with USB 2.0
- Easy Plug-and-Play installation
- Bus powered, no external power adapter required

### Hardware

	Warranty	Lifetime
Ports	4	
Interface	Serial	
Bus Type	USB 2.0	
Port Style	External Hub	
Industry Standards	RS232	
	USB 1.1	
Chipset ID	FTDI - FT232RL	

### Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
FIFO	256 Bytes

### Connector(s)

Connector Type(s)	1 - USB 2.0 Type-A (4 pin, 480Mbps)
External Ports	4 - DB-9 (9 pin, D-Sub)

### Software

OS Compatibility	Windows CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11, 11 ARM
	Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019,

2022, 2025

macOS 10.6 to 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1

Linux Kernel 3.0.x and up - LTS Versions only

---

**Special Notes / Requirements**

System and Cable Requirements	One free USB port
-------------------------------	-------------------

---

**Power**

Power Consumption (In Watts)	1 ~ 1.5W
------------------------------	----------

---

**Environmental**

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-20 to 85C (-4 to 185F)
Humidity	5~95% RH

---

**Physical Characteristics**

Color	Black
Material	Plastic
Cable Length	6.0 ft [1.8 m]
Product Length	5.9 in [15 cm]
Product Width	2.6 in [6.6 cm]
Product Height	1.0 in [2.6 cm]
Weight of Product	5.2 oz [146 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.5 in [21.6 cm]
Package Width	5.9 in [15 cm]
Package Height	2.0 in [5.2 cm]
Shipping (Package) Weight	13.0 oz [368.0 g]

---

**What's in the Box**

Included in Package	1 - 4 Port Serial Hub
	1 - USB Cable
	1 - Mounting Bracket
	1 - Driver CD
	1 - Instruction Manual

---

**Warranty  
Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

