

Universal DC Power Adapter for Industrial USB Hubs - 20V, 3.25A

Product ID: ITB20D3250



This universal DC power adapter has been designed as an alternative, back up or replacement power supply for StarTech.com's line of industrial USB hubs.

10-Port Industrial USB 3.0 Hub with External Power Adapter - ESD & 350W Surge Protection (HB30A10AME)

10-Port Industrial USB 3.0 Hub with ESD & 350W Surge Protection (ST1030USBM)

7-Port Managed USB Hub with 7x USB-A, Heavy Duty with Metal Industrial Housing, ESD & Surge Protection (5G7AINDRM-USB-A-HUB)

7-Port Industrial USB 3.0 Hub with External Power Adapter - ESD & 350W Surge Protection (HB30A7AME)

7-Port Industrial USB 3.0 Hub with ESD & 350W Surge Protection (ST7300USBME)

4 Port USB C Hub 10Gbps - 2x USB-C & 2x USB-A - ESD Surge Protection (HB31C2A2CME)

4-Port Managed USB Hub with 4x USB-A, Heavy Duty w/ Metal Industrial Housing, ESD & Surge Protection (5G4AINDRM-USB-A-HUB)

4-Port Industrial USB 3.0 5Gbps Hub - Rugged USB Hub w/ ESD and Surge Protection (5G4AINDNP-USB-A-HUB)

4-Port Industrial USB 3.0 Hub with ESD Protection (ST4300USBM)

10-Port Industrial USB 2.0 Hub, Rugged USB Hub w/ESD Level 4 Protection (USB210AIND-USB-A-HUB)

7-Port Industrial USB 2.0 Hub ESD Protection & 350W Surge Protection (HB20A7AME)

7-Port Industrial USB 2.0 Hub with ESD & 350W Surge Protection (ST7200USBM)

4-Port Industrial USB 2.0 Hub with ESD Protection & 350W Surge Protection (HB20A4AME)

4-Port Industrial USB 2.0 Hub with ESD Protection (ST4200USBM)

The external terminal power adapter can also be used with any other devices that can support 20V power supply including a variety of StarTech.com Ethernet Switches and Serial Adapters.

Certifications, Reports and Compatibility



Applications

Features

- Terminal block power adapter has been designed for StarTech.com industrial products
- Use as an alternative power source, replacement, or back-up power supply when sufficient bus-power is unavailable
- Includes regional plug attachments for NA/JP, EU, UK & ANZ
- Includes an attached two conductor terminal block
- Includes an additional three conductor terminal block

Performance

Warranty	1 Year
MTBF	300,000 Hours

Indicators

LED Indicators	1 - Green Power LED
----------------	---------------------

Power

Input Voltage	110V-240V AC
Input Current	1.4A Max.
Output Voltage	20V DC
Output Current	3.25A
Plug Type	Terminal Block (2 Wire)
	Terminal Block (3 Wire)

Power Consumption (In Watts) 65W

Environmental

Operating Temperature	+ 0°C ~ + 40°C
Storage Temperature	- 20 °C ~ + 80°C
Humidity	20% ~ 80% RH

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	4.5 in [11.5 cm]
Product Width	2.1 in [5.3 cm]
Product Height	1.5 in [3.7 cm]
Weight of Product	10.3 oz [291.0 g]

Packaging Information

Package Quantity	1
Package Length	9.6 in [24.3 cm]
Package Width	6.7 in [16.9 cm]
Package Height	2.4 in [6.2 cm]
Shipping (Package) Weight	1.9 lb [0.9 kg]

What's in the Box

Included in Package	1 - Universal 65W Power Adapter with 4ft [1.2m] Cable
	4 - 5ft [1.5m] Power Cords (NA/JP, EU, UK, ANZ)
	1 - Two Conductor Terminal Block Connector (Attached)
	1 - Three Conductor Terminal Block Connector
	1 - Quick-Start Guide

Warranty

Information

Warranty	1 Year
----------	--------

**Product appearance and specifications are subject to change without notice.*

