

10ft (3m) Laptop Power Cord, NEMA 5-15P to C5 (Clover Leaf), 10A 125V, 18AWG, Laptop Replacement Cord, Printer Power Cable, Laptop Charger Cord, Laptop Power Brick Cord - UL Listed

**Product ID:** PXT101NB3S10



The PXT101NB3S10 10-foot 3-Slot Laptop Power Cord features one NEMA 5-15P and one C5 connector - a suitable replacement notebook power cord or spare power cord for your HP, Toshiba or other compatible laptop.

## Certifications, Reports and Compatibility



## Applications

- Spare/replacement cable for your laptop
- Laptop accessory for mobile professionals

## Features

- **AC POWER CORD:** This 10ft (3m) 18AWG flexible laptop power cord with NEMA 5-15P and IEC 60320 C5 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief C5 connector for durability. Fire Rating: VW-1 3 Conductor Notebook Power Cable made with 100% Copper Wire
- **SPECS:** 10ft (3m) Power Cable NEMA 5-15P to IEC 60320 C5 18AWG 125V 10A (Max) Jacket Rating: SVT. Jacket Material: PVC. Color: Black. Temperature Range: 35F to 140F (2 to 60). Cable Outer Diameter: 0.3in

(7.62mm)

- **COMPATIBILITY:** AC Power Cord NEMA 5-15P works with North American outlets IEC C5 connector works with most power bricks for laptops/notebooks, monitors, scanners, printers, and more Replacement laptop power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this laptop charger cord is backed for life, including free lifetime 24/5 multilingual technical assistance

---

#### Hardware

|                      |          |
|----------------------|----------|
| Warranty             | Lifetime |
| Number of Conductors | 3        |
| Cable Type           | SVT      |

---

#### Connector(s)

|             |                                     |
|-------------|-------------------------------------|
| Connector A | 1 - NEMA 5-15 Power (North America) |
| Connector B | 1 - IEC 60320 C5 Power              |

---

#### Special Notes / Requirements

|      |           |
|------|-----------|
| Note | UL Listed |
|------|-----------|

---

#### Power

|               |        |
|---------------|--------|
| Input Voltage | 125 AC |
| Input Current | 10A    |

---

#### Physical Characteristics

|                   |                   |
|-------------------|-------------------|
| Color             | Black             |
| Wire Gauge        | 18 AWG            |
| Cable Length      | 10.0 ft [3.0 m]   |
| Product Length    | 10.0 ft [3.0 m]   |
| Product Width     | 1.0 in [2.5 cm]   |
| Product Height    | 0.8 in [2.0 cm]   |
| Weight of Product | 10.4 oz [295.0 g] |

---

#### Packaging Information

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 7.0 in [17.8 cm]  |
| Package Width             | 7.8 in [19.9 cm]  |
| Package Height            | 1.7 in [4.2 cm]   |
| Shipping (Package) Weight | 11.1 oz [314.0 g] |

---

**What's in the Box**

|                     |   |
|---------------------|---|
| Included in Package | 1 - 10 ft Standard Laptop Power Cord - NEMA 5-15P to C5 |
|---------------------|---|

---

**Warranty Information**

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

*\*Product appearance and specifications are subject to change without notice.*

