

3ft (1m) Heavy Duty Power Cord, NEMA 5-15P to C19 AC Power Cord, 15A 125V, 14AWG, Computer Power Cord, Heavy Gauge Power Cable for PDUs and Network Equipment, NEMA 5-15P to IEC 60320 C19 Power Cord

Product ID: PXT515C19143



This NEMA 5-15P-to-C19 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for high-end server equipment such as routers, switches, Power Distribution Units (PDU), etc.

Plus, you can use the cable to extend the reach of your existing power cord by 3 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXT515C19143 power cord is backed by a lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect your high-power server equipment to a power outlet
- Extend your existing power cord by 3 feet

Features

- **HEAVY DUTY AC POWER CORD:** This 3ft (1m) 14AWG universal power cord with NEMA 5-15P and IEC 60320

C19 connectors is suitable for workstations/home office use. Rated to carry 125V at 15A.

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability. Fire Rating: VW-1 3 Conductor Power Cable made with 100% Copper Wire. This C19 thick gauge computer power cord is available in other lengths.
- **SPECS:** 3ft (1m) AC Power Cord NEMA 5-15P to IEC 60320 C19 14AWG 125V 15A (Max) Jacket Type: SJT. Jacket Material: PVC Black. Temperature Range: 37F to 167F (3C to 75C) Cable Outer Diameter: 0.36in (9.1mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets. IEC C19 connector works with most servers and networking equipment. Replacement PC power supply cable/cord.
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance.

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C19 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]

Weight of Product	6.8 oz [192 g]
-------------------	----------------

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.9 cm]
Package Width	3.0 in [7.7 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	7.0 oz [198.0 g]

What's in the Box

Included in Package	1 - 3 ft 14 AWG Computer Power Cord - NEMA 5-15P to IEC 320 C19
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*