

## 7 Port Compact Black USB 2.0 Hub - TAA

**Product ID:** ST7202USB



This TAA compliant 7 Port USB 2.0 Hub connects to one USB 2.0 port on a Mac or PC computer, adding seven USB 2.0 ports - allowing you to maximize the number of high speed USB peripherals connected to your computer. The hub supports cascaded installation with other USB 2.0 hubs, supporting up to 127 USB 2.0 device connections - a scalable solution for connecting multiple USB devices to a single host computer.

The 7 port hub includes a power adapter, but can be powered through USB bus connection to the host computer - allowing you to install the hub as needed without worrying about the availability of a power outlet.

### Certifications, Reports and Compatibility



### Applications

- Charge iPod's or other portable devices that can be recharged through USB 2.0
- Add additional USB 2.0 ports to a computer to connect more devices
- Move USB ports further away from the computer chassis with an external hub
- Make hard to reach USB ports more accessible, by being able to position the hub anywhere the cable will reach

## Features

- TAA Compliant
- High Speed USB 2.0 compliant, with supported data transfer rates up to 480 Mbps
- Backwards compatible with USB 1.1/1.0 devices
- Over current protection on each port
- Includes optional external power adapter
- Compact and light-weight design
- Plug and Play and Hot Swap compatible

---

### Hardware

Warranty	2 Years
Ports	7
Interface	USB 2.0
Chipset ID	Genesys Logic - GL850G

---

### Performance

Maximum Data Transfer Rate	480 Mbps
MTBF	68,587 hours

---

### Connector(s)

External Ports	7 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - USB B (4 pin)

---

### Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

---

### Special Notes / Requirements

System and Cable Requirements	1 x Free USB port
-------------------------------	-------------------

---

### Power

Power Source	AC Adapter Included
--------------	---------------------

---

Input Voltage	100 - 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	10

---

#### **Environmental**

Operating Temperature	0 to 70 C
Storage Temperature	-55 to 100 C
Humidity	20% ~ 80% Relative Humidity

---

#### **Physical Characteristics**

Color	Black
Material	Plastic
Product Length	3.9 in [10.0 cm]
Product Width	2.4 in [6.0 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	2.7 oz [77.0 g]

---

#### **Packaging Information**

Package Quantity	1
Package Length	5.8 in [14.7 cm]
Package Width	8.3 in [21.1 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	10.5 oz [298.0 g]

---

**What's in the Box**

Included in Package	1 - 7 Port USB 2.0 Hub
	1 - USB 2.0 Cable
	1 - Power Adapter
	1 - Instruction Manual

---

**Warranty  
Information**

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***

