

6 Port USB 3.0 / USB 2.0 Combo Hub with 2A Charging Port – 2x USB 3.0 & 4x USB 2.0

Product ID: ST7320USBC



The ST7320USBC 6-Port USB 3.2 Gen 1/2.0 Combo Hub features a special high-output dedicated charging port which enables you to charge USB devices by providing up to 2A of power, or it can add 2x USB 3.2 Gen 1 and 4x USB 2.0 ports to a computer through a single USB 3.2 Gen 1 host connection.

The hub includes an external power adapter, which when connected enables charging some portable electronic devices (e.g. an iPhone or other Smartphone), even without a USB connection to a host computer.

Offering a unique design that features USB ports along 3 sides of the hub, as well as a combination of USB 2.0 and 3.0 ports, this versatile and flexible USB hub is ideal for both laptop and desktop computers.

The ST7320USBC USB 3.2 Gen 1/2.0 hub is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add multiple USB 3.0 and USB 2.0 to a computer system to support more device connections

- Charge a Smartphone
- Charging high-powered portable devices (such as tablets) which require special high output USB ports for charging
- Make USB ports that are hard to access more accessible, by being positioning the hub in a convenient location (within cable reach)
- Extend the range of a USB device by having the hub act as a mid-point repeater

Features

- 2x USB 3.2 Gen 1 and 4x USB 2.0 ports that can be all accessed simultaneously
- 2 Amp high output USB Dedicated Charging Port (DCP)
- Includes 20 watt power adapter and host USB 3.2 Gen 1 cable
- Universal, multi-platform compatible, with no additional drivers or software required
- SuperSpeed USB 3.2 Gen 1 compliant host interface, with support for up to 5 Gbps of data bandwidth

Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	Yes
Ports	7
Interface	USB 3.2 Gen 1 (5Gbps)
Bus Type	USB 3.2 Gen 1 (5Gbps)
	USB 3.2 Gen 1 (5Gbps)
Chipset ID	VIA/VLI - VL817

Performance

Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
	USB 3.2 Gen 1 - 5 Gbit/s

Connector(s)

External Ports	2 - USB Type-A (9 pin, 5 Gbps)
----------------	--------------------------------

1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

4 - USB 2.0 Type-A (4 pin, 480Mbps)

Software

OS Compatibility	OS Independent
------------------	----------------

Special Notes / Requirements

System and Cable Requirements	Available USB 3.0 or 2.0 port
-------------------------------	-------------------------------

Indicators

LED Indicators	1 - Power
----------------	-----------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.5 A
Output Voltage	5 DC
Output Current	4 A
Plug Type	H
Power Consumption (In Watts)	20

Environmental

Operating Temperature	0C to 85C (32F to 185F)
Storage Temperature	-10C to 95C (14F to 203F)
Humidity	5~90% RH

Physical Characteristics

Color	Black
Form Factor	Desktop
Material	Plastic
Product Length	3.9 in [99.0 mm]

Product Width	2.4 in [6.0 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	2.6 oz [74.0 g]

Packaging Information

Package Quantity	1
Package Length	4.8 in [12.1 cm]
Package Width	5.5 in [13.9 cm]
Package Height	4.1 in [10.4 cm]
Shipping (Package) Weight	1.0 lb [0.5 kg]

What's in the Box

Included in Package	1 - 6 Port USB Hub
	1 - USB 3.0 Cable
	4 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
	1 - Instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

