

USB to 5.5mm Power Cable - Type M Barrel - 2m

Product ID: USB2TYPEM2M



Tired of having to carry around a separate wall adapter in order to power or charge your 5V devices, such as certain external hard drives, streaming media players, and Bluetooth speakers?

This 2m USB power cable makes it easier to power 5V DC devices that have a Type M (OD: 5.5mm, ID: 2.1mm) barrel power connector. You can power or charge the devices through an available USB port on your laptop or desktop computer.

Expertly designed and constructed of high-quality materials, the StarTech.com USB2TYPEM2M power cable is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Power your external hard drive or other devices that are equipped with a Type-M power connector through an available USB port on your computer
- Charge your Bluetooth speakers and other chargeable devices through an available USB port on your computer

Features

- DURABLE: 6.6ft (2.0m) USB-A to Type M (5.5mm outer diameter, 2.1mm inner diameter, center pin positive) coaxial barrel connector cable; This power cable can be used to power any M barrel device at 5V from a standard

USB supplying up to 0.9A

- **COMPATIBILITY:** Only works with M barrel connections measuring 5.5 OD by 2.1 ID with a positive center pin; The connected device must use 5V, and a max current of 0.9A; Current supplied is determined by the USB port this cable is plugged into
- **DURABLE:** This type-M coaxial power barrel connector (fully molded) with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying/damage due to repetitive bending or rough usage
- **SPECS:** Length: 6.6ft (2.0m); USB-A; Type M coaxial power (Barrel Power Connector OD:5.50, ID: 2.10); Jacket: PVC; Outer Diam (OD): 4.5mm; 5V at up to 0.9A supplied by a USB port; Aluminum-mylar foil with braided shielding
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB to 5.5MM power cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	1 - USB 2.0 Type-A
Connector B	1 - Barrel Power Connector (Size M, OD:5.50, ID: 2.10)

Power

Center Tip Polarity	Positive
---------------------	----------

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Wire Gauge	24 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.0 ft [1.8 m]

Product Width	0.6 in [1.5 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	1.6 oz [45.0 g]

Packaging Information

Package Quantity	1
Package Length	5.6 in [14.3 cm]
Package Width	5.0 in [12.7 cm]
Package Height	0.7 in [1.9 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

What's in the Box

Included in Package	1 - 2 m USB to Type M Barrel 5V DC Power Cable
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

