

1 ft SuperSpeed USB 3.0 (5Gbps) Cable A to B - M/M

Product ID: USB3SAB1



StarTech.com's 1-foot USB 3.2 Gen 1 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the 1-foot USB 3.2 Gen 1 cable supports a throughput of up to 5Gbps when used with a USB 3.2 Gen 1 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 1-foot USB 3.2 Gen 1 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 1ft USB 3.2 Gen 1 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility



Applications

- Connect a SuperSpeed USB 3.0 device (Hubs, external storage device) to an USB 3.0 capable PC, laptop, or Server

Features

- Shielded Twisted Pair (STP) design which prevents electro-magnetic interference (EMI)
- Support for data transfer rates up to 5Gbps - 10x faster than USB 2.0

- Backward compatible with USB 2.0
- Nickel-plated connectors

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

Physical Characteristics

Color	Blue
Wire Gauge	28 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	1.0 ft [0.3 m]
Weight of Product	0.9 oz [26 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.4 in [11 mm]
Shipping (Package) Weight	1.2 oz [35 g]

What's in the Box

Included in Package	1 - 1 ft SuperSpeed USB 3.0 Cable A to B - M/M
---------------------	--

**Warranty
Information**

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

