

Micro-USB Charge-and-Sync Cable M/M - Left-Angle Micro-USB - 24 AWG - 0.5 m

**Product ID:** USBAUB50CMLA



This Micro-USB cable features 24 AWG wire to provide the full power you need to charge your mobile devices faster. The cable features a left-angled Micro-USB connector, so it's great for charging your mobile devices in a car, or for accessing your mobile device while it's connected to a car charger or computer.

Different phones and tablets require specific amounts of power to charge efficiently. While a phone may only require 1.0A of power, a tablet may need 2.4A.

This Micro-USB cable is designed to deliver full power to your mobile devices so that all of your devices can charge at the expected speed.

The left-angled Micro-USB connector lets you connect to ports that are difficult to reach, which is perfect for charging your car-mounted mobile devices. Even while you're charging your mobile device, you can use it to text, work or game, without the cable getting in the way.

The angled connector also prevents the cable from bending awkwardly or from straining too much to make a connection. It offers a more natural fit at the connection point, preventing unnecessary stress and damage to the cable and device port.

Replace the Micro-USB cable that came with your mobile device, or keep one as a spare while you're traveling so that your mobile devices are ready to use while you're on the road. The short 0.5 m/1.5 ft. cable length makes this an excellent solution for close-range connections and portable applications such as charging with a mobile charging bank, public charging stations or your laptop.

The USBAUB50CMLA 0.5-meter cable is backed by StarTech.com's lifetime warranty for guaranteed reliability.

## Certifications, Reports and Compatibility



## Applications

- Charge and sync your Micro-USB mobile devices
- Replace the cable that came with your Micro-USB device or keep one as a spare while traveling

## Features

- Provide full charging power to your Micro-USB mobile devices
- Connect to your device even in hard to reach areas and tight spaces
- Portable design fits nicely into any carrying case

### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

### Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

### Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB Micro-B (5 pin)

### Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

### Physical Characteristics

Color	Black
-------	-------

---

Connector Style	Straight to Left Angle
Wire Gauge	24/30 AWG
Cable Length	1.6 ft [0.5 m]
Product Length	19.2 in [48.8 cm]
Product Width	0.6 in [1.5 cm]
Product Height	0.7 in [1.8 cm]
Weight of Product	0.6 oz [18.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	4.9 in [12.4 cm]
Package Width	2.8 in [7.1 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	0.9 oz [26.0 g]

---

**What's in the Box**

Included in Package	1 - Micro-USB Cable
---------------------	---------------------

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

