

Standalone 1 to 7 USB Thumb Drive Duplicator and Eraser, Multiple USB Flash Drive Copier, System and File and Whole-Drive Copy at 1.5 GB/min, Single and 3-Pass Erase, LCD Display - TAA

Product ID: USBDUPE17



This USB duplicator and eraser lets you clone or erase up to seven USB flash drives, without a host computer connection. This means you can work more efficiently and manage larger batches of USB drives, saving time and effort.

The standalone USB duplicator and eraser is perfect for IT professionals and system administrators in corporate, education, marketing, or sales environments.

Efficient 1:7 drive duplication

The duplicator lets you copy up to seven drives simultaneously, and offers both synchronous and asynchronous duplication, with speeds up to 1.5GB per minute. The asynchronous feature means you can remove and replace USB storage devices while other copies continue to run. The eraser/duplicator offers two modes of duplication: system and file and whole file.


Erase multiple USB drives simultaneously

The drive duplicator/eraser lets you erase up to seven flash drives at the same time, so it's easy to clean large batches of USB drives for reuse. The flash drive duplicator features three modes of erasing: quick erase, single pass erase, and multi-pass erase (meets DoD standards).

Designed for ease of use

The flash drive duplicator and eraser supports USB 3.0, USB 2.0 and USB 1.1 flash drives, providing an easy and cost-effective way to re-use and re-purpose your USB drives. It features a robust metal housing and a compact, standalone design that makes it the perfect desktop companion. The duplicator/eraser also has an LCD display that makes it easy to monitor erasing and duplication to ensure completion.

Certifications, Reports and Compatibility



Applications

- Software and operating system update rollouts
- Marketing collateral copying and distribution
- Backup USB flash drives without a host computer
- Clean and prepare USB drives for reuse
- Testing and evaluating USB drives
- Professionals who require identical backups for when data integrity is crucial, such as data recovery
- IT administrators who wish to erase multiple drives simultaneously in preparation for use in other applications

Features

- DUPLICATE & ERASE USB DRIVES: Standalone 1 to 7 USB drive duplicator / cloner / sanitizer; Ideal for technicians and IT Pros to manage multiple USB boot drives, wipe USB drives, or quickly share data between teams; No Computer required
- DRIVE COMPATIBILITY: Supports cloning/duplication and erasing of USB 3.0/2.0 flash media thumb drives and USB External Storage (External USB device(s) may require its own power source connecting to outlets); Firmware is upgradeable
- DUPLICATION AND ERASE MODES: 1.5 GB/min System & File Copy (FAT16/32, NTFS, Linux ext2, ext3, ext4 formats), whole-drive Sector-by-Sector Copy (all file formats), Quick Erase, Single-Pass & 3-Pass Overwrite (DoD/NIST SP 800-88 Rev 1 Clear); TAA Compliant
- LCD MENU DISPLAY: Use push button interface to monitor drive info, read & write performance, and scan drive for errors and bad sectors; Select Copy & Compare to verify your cloned drives with source when complete; Green/Red LEDs for activity/errors
- ASYNCHRONOUS COPY MODE: Quickly copy to multiple USB thumb drives using Asynchronous Copy mode w/ 128 MB internal memory; Source content must be under 128 MB; Remove your finished drive and insert a new drive to start copying without interruptions

Hardware

Warranty

2 Years

| | |
|------------------------|-----------------------------|
| Bus Type | USB 2.0 |
| Number of Drives | 7 |
| Compatible Drive Types | USB Flash Drive |
| Drive Installation | Removable |
| Chipset ID | Xilinx - Spartan (XC3S700A) |
| Buffer Size | 128 MB |

Performance

| | |
|--------------------|---|
| Duplication Modes | System and File |
| | Sector by Sector (Whole Drive) |
| Duplication Speed | 1.5GBpm |
| Erase Modes | Quick Erase |
| | 1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear) |
| | 3-Pass Overwrite |
| Max Drive Capacity | 3TB |
| Insertion Rating | 1500 times |
| MTBF | 176,549 hours |

Connector(s)

| | |
|------------------|-------------------------------------|
| Drive Connectors | 8 - USB 2.0 Type-A (4 pin, 480Mbps) |
|------------------|-------------------------------------|

Software

| | |
|------------------|---|
| OS Compatibility | OS independent; No software or drivers required |
|------------------|---|

Special Notes / Requirements

| | |
|-------------------------------|--|
| System and Cable Requirements | For duplication, the destination drives must be of equal or greater capacity than the source drive. |
| | For erasing, only the destination ports are active, the source port cannot be used. This helps to prevent erasing a source drive accidentally. |
| | Supports copying/cloning/erasing to Hard Drives or Solid State Drives through a Hard Drive docking station or USB enclosure |

(sold separately) if supported by the storage media

Indicators

| | |
|----------------|--------------------------------------|
| LED Indicators | 8 - Green (Activity/Successful Copy) |
| | 8 - Red (Error) |

Power

| | |
|------------------------------|---------------------|
| Power Source | AC Adapter Included |
| Input Voltage | 100 - 240 AC |
| Input Current | 1.6A Max |
| Output Voltage | 12V DC |
| Output Current | 9A |
| Plug Type | 4-pin DIN |
| Power Consumption (In Watts) | 108W |

Environmental

| | |
|-----------------------|------------------------|
| Operating Temperature | 5C ~ 45C (41F ~ 113F) |
| Storage Temperature | -20C ~85C (-4F ~ 185F) |
| Humidity | 20% ~ 80% |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Material | Steel |
| Product Length | 7.5 in [19 cm] |
| Product Width | 6.3 in [16 cm] |
| Product Height | 1.4 in [3.5 cm] |
| Weight of Product | 2.3 lb [1.0 kg] |

Packaging Information

| | |
|------------------|---|
| Package Quantity | 1 |
|------------------|---|

| | |
|---------------------------|-------------------|
| Package Length | 18.5 in [47.0 cm] |
| Package Width | 9.3 in [23.7 cm] |
| Package Height | 3.7 in [9.5 cm] |
| Shipping (Package) Weight | 6.7 lb [3.0 kg] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1 - duplicator and eraser |
| | 1 - universal power adapter (NA/JP, UK, EU, ANZ) |
| | 1 - instruction manual |

Warranty Information

| | |
|----------|---------|
| Warranty | 2 Years |
|----------|---------|

**Product appearance and specifications are subject to change without notice.*

