

1 ft Panel Mount USB Cable A to A - F/M

Product ID: USBPNLAFAM1



The USBPNLAFAM1 1ft Panel Mount USB Cable provides a well-secured, easy to access USB-A port on your PC or on a faceplate, allowing you to customize your systems to suit your needs. Perfect for podiums, kiosks and other solutions where added access to USB devices is required.

The adapter features one male USB-A connector and one female panel mount USB-A port and gives you an extension of 1ft, enabling you to place the cable as needed within the system case.

The USBPNLAFAM1 is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Add a USB-A female port to the back of your PC or on a faceplate

Features

- 1x USB-A male connector
- 1x USB-A panel mount female port
- Offers 1' in cable length

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Wire Gauge	24/28 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	12.0 in [30.5 cm]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	0.9 oz [26.0 g]

Packaging Information

Package Quantity	1
Package Length	5.6 in [14.2 cm]
Package Width	5.0 in [12.7 cm]
Package Height	0.6 in [1.5 cm]
Shipping (Package) Weight	1.0 oz [28.0 g]

What's in the Box

Included in Package 1 ft Panel Mount USB Cable A to A - F/M

**Warranty
Information**

Warranty Lifetime

****Product appearance and specifications are subject to change without notice.***

