

1 ft Panel Mount USB Cable B to B - F/M

Product ID: USBPNLBFBM1



The USBPNLBFBM1 USB B to USB Panel mount cable features a USB type B male connector on one end, and a USB panel mount B (female) molded connector on the other, providing a convenient solution for custom enclosures (e.g. internally mounted hard drives).

The USB panel mount cable (B-B) is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

Features

- Standard size Molded hood for easy screw-in installation
- Shielded to prevent EMI / RFI interference
- Compliant with USB 2.0 specifications

Hardware

Warranty

Lifetime

Cable Jacket Material PVC - Polyvinyl Chloride

Connector(s)

Connector A	USB B (4 pin)
Connector B	USB B (4 pin)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Cable Length	1.0 ft [0.3 m]
Product Length	12.0 in [30.5 cm]
Product Width	1.4 in [3.5 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	1.0 oz [29.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	1.4 in [3.6 cm]
Shipping (Package) Weight	1.2 oz [34.5 g]

What's in the Box

Included in Package	1 ft Panel Mount USB Cable B to B - F/M
---------------------	-----------------------------------------

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

