

1ft Micro USB Cable - A to Micro B

**Product ID:** UUSBHAUB1



The UUSBHAUB1 1-foot USB A to Micro USB cable features one USB 'A' male connector, and one 'Micro-B' male connector, providing a high quality connection to USB 2.0 mobile devices (such as BlackBerry or Android-based cellular phones, digital cameras, Tablet PC devices and GPS systems) that use a Micro USB connector to a USB capable computer for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

## Certifications, Reports and Compatibility



## Applications

- An ideal replacement cable for connecting mobile devices to a USB capable computer

## Features

- Supports high speed data transfer rates up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding
- High quality USB 'A' and USB 'Micro-B' connectors
- Durable PVC construction

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Connector(s)**

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB Micro-B (5 pin)

---

**Environmental**

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

---

**Physical Characteristics**

Color	Black
Wire Gauge	24/30 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	12.0 in [30.5 cm]
Product Width	0.6 in [1.6 cm]
Product Height	0.3 in [0.7 cm]
Weight of Product	0.6 oz [17.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.6 in [14.3 cm]
Package Width	5.1 in [13.0 cm]
Package Height	0.4 in [1.1 cm]

Shipping (Package) 0.6 oz [16.0 g]  
Weight

---

**What's in the Box**

Included in Package 1 - 1ft Micro USB Cable - A to Micro B

---

**Warranty  
Information**

Warranty Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*

