

## 1 ft Micro USB Cable - A to Left Angle Micro B

**Product ID:** UUSBHAUB1LA



The UUSBHAUB1LA 1-foot USB-A to Micro-B Cable provides a high quality connection between Micro USB-equipped USB 2.0 mobile devices (such as BlackBerry or Android-based smart phones, digital cameras, PDAs, Tablet PC devices and GPS systems, etc.) and a USB-capable computer, for everyday tasks such as data synchronization, file transfers and charging.

The left-angled Micro USB connector positions the cable in such a way that it allows you to easily access your mobile digital device in both portrait and landscape mode, even while charging.

Designed and constructed for maximum durability, this high quality USB-A to Left Angle Micro-B cable is backed by StarTech.com's Lifetime Warranty.

As an alternative, StarTech.com also offers a 1ft USB A to Right Angle Micro B Cable (UUSBHAUB1RA), which provides the same convenience as this left-angled cable but allows you to connect to your USB Micro-B devices from the opposite direction.

## Certifications, Reports and Compatibility



## Applications

- Transfer data, connect to various USB devices, and provide power while charging your Micro USB device, without the cable getting in the way

## Features

- 1x USB 'A' male connector
- 1x Left Angle USB Micro-B male connector
- Supports high-speed data transfer rates of up to 480 Mbps
- Molded connectors with strain relief

---

**Hardware**

|                       |                          |
|-----------------------|--------------------------|
| Warranty              | Lifetime                 |
| Cable Jacket Material | PVC - Polyvinyl Chloride |

---

**Performance**

|               |                      |
|---------------|----------------------|
| Type and Rate | USB 2.0 - 480 Mbit/s |
|---------------|----------------------|

---

**Connector(s)**

|             |                                     |
|-------------|-------------------------------------|
| Connector A | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |
| Connector B | 1 - USB Micro-B (5 pin)             |

---

**Environmental**

|                       |                           |
|-----------------------|---------------------------|
| Operating Temperature | -20C to 60C (-4F to 140F) |
| Storage Temperature   | -10C to 30C (14F to 86F)  |
| Humidity              | 30%-75% RH                |

---

**Physical Characteristics**

|                   |                        |
|-------------------|------------------------|
| Color             | Black                  |
| Connector Style   | Straight to Left Angle |
| Wire Gauge        | 24/30 AWG              |
| Cable Length      | 1.0 ft [0.3 m]         |
| Product Length    | 12.4 in [31.6 cm]      |
| Product Width     | 0.7 in [1.8 cm]        |
| Product Height    | 0.3 in [0.8 cm]        |
| Weight of Product | 0.5 oz [14.0 g]        |

**Packaging  
Information**

|                              |                  |
|------------------------------|------------------|
| Package Quantity             | 1                |
| Package Length               | 6.1 in [15.4 cm] |
| Package Width                | 5.1 in [12.9 cm] |
| Package Height               | 0.6 in [1.5 cm]  |
| Shipping (Package)<br>Weight | 0.8 oz [22.0 g]  |

---

**What's in the Box**

|                     |  |
|---------------------|--|
| Included in Package | 1 - 1 ft Micro USB Cable - A to Left Angle Micro B |
|---------------------|--|

---

**Warranty  
Information**

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

*\*Product appearance and specifications are subject to change without notice.*

