

6in Micro USB Cable - A to Micro B

Product ID: UUSBHAUB6IN



The UUSBHAUB6IN 6-inch USB A to Micro-B cable provides a high quality connection between Micro USB-equipped USB 2.0 mobile devices (such as BlackBerry or Android-based smart phones, digital cameras, PDAs, Tablet PC devices and GPS systems) and a USB-capable computer, for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

Certifications, Reports and Compatibility



Applications

- An ideal replacement cable for connecting mobile devices to a USB capable computer

Features

- 1x USB 'A' male connector
- 1x USB Micro 'B' male connector
- Offers 6" in cable length
- Aluminum-Mylar Foil with Braided Shielding

- Supports high-speed USB data transfer rates of up to 480 Mbps

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB Micro-B (5 pin)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Wire Gauge	24/30 AWG
Cable Length	6.0 in [152 mm]
Product Length	6.0 in [15.2 cm]
Product Width	0.6 in [1.5 cm]
Product Height	0.3 in [0.8 cm]
Weight of Product	0.4 oz [10.0 g]

Packaging Information

Package Quantity	1
Package Length	4.0 in [10.2 cm]
Package Width	5.1 in [12.9 cm]

Package Height 0.8 in [2.1 cm]

Shipping (Package) Weight 0.6 oz [16.0 g]

What's in the Box

Included in Package 1 - 6in Micro USB Cable - A to Micro B

**Warranty
Information**

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

